



●標準寸法では、突き出し長さが不足するような場合に使用します。

This tap is used when a standard TAFLET-L is too short.



LIST 6970 NACHI-TDT

オーダ方法

切削条件 Cutting Condition → C-30

TFLL 記号 × 等級 × 食付 × 全長

単位 (Unit) : mm / 円 (¥)

記号 Code No.	等級 TAP Limit	食付 (P) Lc (P)	全長 L	呼び Thread Size	ねじ長 ℓ	ラジアル数 Radial	シャンク径 Ds	形式 Type	在庫 Stock	参考価格 Price
3M0.5	5	B	70	M3 X 0.5	18	4	4	1	●	1,800
3M0.5	5	B	100	M3 X 0.5	18	4	4	1	●	2,480
3M0.5	5	B	120	M3 X 0.5	18	4	4	1	●	2,870
4M0.7	6	B	70	M4 X 0.7	20	4	5	1	●	1,580
4M0.7	6	B	100	M4 X 0.7	20	4	5	1	●	2,240
4M0.7	6	B	120	M4 X 0.7	20	4	5	1	●	2,700
5M0.8	6	B	100	M5 X 0.8	22	4	5.5	1	●	2,010
5M0.8	6	B	120	M5 X 0.8	22	4	5.5	1	●	2,480
5M0.8	6	B	150	M5 X 0.8	22	4	5.5	1	●	3,140
6M1	7	B	100	M6 X 1	24	4	6	2	●	1,910
6M1	7	B	120	M6 X 1	24	4	6	2	●	2,010
6M1	7	B	150	M6 X 1	24	4	6	2	●	2,890
8M1.25	7	B	100	M8 X 1.25	30	4	6.2	3	●	2,130
8M1.25	7	B	120	M8 X 1.25	30	4	6.2	3	●	2,370
8M1.25	7	B	150	M8 X 1.25	30	4	6.2	3	●	3,490
10M1.5	7	B	100	M10 X 1.5	32	4	7	3	●	2,600
10M1.5	7	B	120	M10 X 1.5	32	4	7	3	●	2,890
10M1.5	7	B	150	M10 X 1.5	32	4	7	3	●	4,040
10M1.25	7	B	100	M10 X 1.25	32	4	7	3	●	2,600
10M1.25	7	B	120	M10 X 1.25	32	4	7	3	●	2,890
10M1.25	7	B	150	M10 X 1.25	32	4	7	3	●	4,040

包装数量 Packed quantity

呼び Thread Size	数量 Pcs.
M3 ~ M 6	10
M8 ~ M10	5