

ATRA ACE Specifications



CLA-2720



LO-3550



WA-3500



WA-5000

Specifications

Model		CLA-2720	LO-3550	WA-3500		WA-5000						
Electric Drill	Power Source (Single Phase)	Battery (18 V DC)	220 - 240 V AC, 50/60 Hz	110 - 120 V AC, 50/60 Hz	220 - 240 V AC, 50/60 Hz	110 - 120 V AC, 50/60 Hz		220 - 240 V AC, 50/60 Hz				
	Rated Power Consumption W	-	800	1100		1150						
	Rated Current A	-	3.3	10.2	5.1	10.8		5.4				
	No-load Speed min ⁻¹ (rpm)	430	950	950		350 / 650						
Magnet Power Consumption W		18	35	34		75						
Max. Hole Diameter mm		27	35	35		50						
Max. Plate Thickness mm		20	50	50		75						
Hole Capacity	One-touch Type JETBROACH	Hole Diameter mm	12 to 17	17.5 to 27	12 to 35		17.5 to 35		12 to 17	17.5 to 40	12 to 50	17.5 to 50
		Plate Thickness mm	6 to 12	6 to 20	6 to 50		9 to 50		9 to 25	9 to 35	9 to 50	9 to 75
	Side-lock Type JETBROACH	Hole Diameter mm	-	-	-		-		-			
		Plate Thickness mm	-	-	-		-		-			
	One-touch Type HI-BROACH	Hole Diameter mm	12 to 15	16 to 27	-		14 to 35		14 to 50			
		Plate Thickness mm	6 to 12	6 to 20	-		9 to 25		9 to 50			
Twist Drill	Hole Diameter mm	-	-	-		-		-				
Max. Stroke mm		60	80	83		107						
Magnet Holding Power N(kgf)		5500 (561)	5500 (561)	7056 (720)		9800 (1000)						
Magnet Dimensions mm		65 x 126	65 x 145	92 x 213		101 x 201						
Overall dimensions * (length) x (width) x (height) mm		199 x 151 x 290	339 x 112 x 316	409 x 237 x 530		425 x 237 x 604						
Power Cord Length m		-	3	3		3						
Mass (Weight) kg		7	8.7	20		23						
Feeding		Manual	Manual	Automatic		Automatic						
Page		7	9	11		11						

*The height is the dimension from the surface of the workpiece to the highest part of the machine when the tip of the Pilot Pin is touching the workpiece with the cutter of the machine's maximum capacity attached.