


## ●穴あけ精度が高く、耐久損性に優れています。

High-precision drilling and superior resistance to chipping.



## ●チップ Inserts

LIST 9824

オーダー方法 商品記号

単位 (Unit) : mm / 円 (¥)

商品記号 Code	直径 Dc	(A)	T	在庫 Stock	参考価格 Price	適用ホルダ Applicable Holder
TVF1400	14.0	11.4	4.5		8,860	AQDEXVF1.5D14 AQDEXVF3D14 AQDEXVF5D14 AQDEXVF8D14
TVF1410	14.1				8,860	
TVF1420	14.2				8,860	
TVF1430	14.3				8,860	
TVF1440	14.4				8,860	
TVF1450	14.5				8,860	
TVF1460	14.6	11.5	4.8		9,770	AQDEXVF1.5D15 AQDEXVF3D15 AQDEXVF5D15 AQDEXVF8D15
TVF1470	14.7				9,770	
TVF1480	14.8				9,770	
TVF1490	14.9				9,770	
TVF1500	15.0				9,770	
TVF1510	15.1				9,770	
TVF1520	15.2	12.4	5.0		9,770	AQDEXVF1.5D16 AQDEXVF3D16 AQDEXVF5D16 AQDEXVF8D16
TVF1530	15.3				9,770	
TVF1540	15.4				9,770	
TVF1550	15.5				9,770	
TVF1560	15.6				9,770	
TVF1570	15.7				9,770	
TVF1580	15.8	13.2	5.5		9,770	AQDEXVF1.5D17 AQDEXVF3D17 AQDEXVF5D17 AQDEXVF8D17
TVF1590	15.9				9,770	
TVF1600	16.0				9,770	
TVF1610	16.1				9,770	
TVF1620	16.2				9,770	
TVF1630	16.3				9,770	
TVF1640	16.4	13.5	5.8		9,770	AQDEXVF1.5D18 AQDEXVF3D18 AQDEXVF5D18 AQDEXVF8D18
TVF1650	16.5				10,680	
TVF1660	16.6				10,680	
TVF1670	16.7				10,680	
TVF1680	16.8				10,680	
TVF1690	16.9				10,680	
TVF1700	17.0	14.2	6.0		10,680	AQDEXVF1.5D19 AQDEXVF3D19 AQDEXVF5D19 AQDEXVF8D19
TVF1710	17.1				10,680	
TVF1720	17.2				10,680	
TVF1730	17.3				10,680	
TVF1740	17.4				10,680	
TVF1750	17.5				10,680	
TVF1760	17.6	15.1	6.5		10,680	AQDEXVF1.5D20 AQDEXVF3D20 AQDEXVF5D20 AQDEXVF8D20
TVF1770	17.7				10,680	
TVF1780	17.8				10,680	
TVF1790	17.9				10,680	
TVF1800	18.0				10,680	
TVF1810	18.1				10,680	
TVF1820	18.2	15.7	6.7		10,680	AQDEXVF1.5D21 AQDEXVF3D21 AQDEXVF5D21 AQDEXVF8D21
TVF1830	18.3				10,680	
TVF1840	18.4				10,680	
TVF1850	18.5				10,680	
TVF1860	18.6				10,680	
TVF1870	18.7				10,680	
TVF1880	18.8	20.0			10,680	
TVF1890	18.9				10,680	
TVF1900	19.0				10,680	
TVF1910	19.1				10,680	
TVF1920	19.2				10,680	
TVF1930	19.3				10,680	
TVF1940	19.4	20.5			10,680	
TVF1950	19.5				10,680	
TVF1960	19.6				10,680	
TVF1970	19.7				10,680	
TVF1980	19.8				10,680	
TVF1990	19.9				10,680	
TVF2000	20.0	21.0			10,680	
TVF2050	20.5				10,680	
TVF2100	21.0				10,680	
TVF2110	21.1				11,800	
TVF2120	21.2				11,800	
TVF2150	21.5				11,800	