

E3000 CONTROLLER



E3000 SELECTOR

Specifications

DXF data

DXF files are available on our website

Order by Code No.

EMA-3020K




Code No.

7874


Model

EMA-3020K

O.D.	Max. speed at the cutting tool	Reduction ratio	Max. rpm
Ø30mm	21,300 min ⁻¹	$\frac{1}{1.5}$	32,000 min ⁻¹
Spindle Accuracy	Collet	Max. power	Weight
Within 2 μm	CHK Group (ø0.5 ~ ø6.35mm)	280w	760g
Standard Accessories	Collet nut (K-265) / Wrench (12×14) : 2pcs. Grease for Speed reducer (10mℓ) / Grease nipple : 1pc.		
Options	Collet (CHK Group) : ø0.5 ~ ø6.35mm p.51 Motor cord : Length 3m (1778), 4m (1768), 6m (1767), 8m (1766) Metal Saw Arbor (KCH-03) : ød (I.D.) × under ø30mm (O.D.) / Grindstone Arbor (AGM-03) : Grindstone I.D. ø5.0mm		



※ Joint type motor cord is necessary.



※ Collet is sold separately.



Put grease every 70 to 100 hours to extend the life of the Speed reducer.

Grease-up prevents friction of the internal gears and degradation of the existing grease in the reducer.

EMA-3020S




Code No.

1758

Model

EMA-3020S

O.D.	Max. speed at the cutting tool	Reduction ratio	Max. rpm
Ø30mm	21,300 min ⁻¹	$\frac{1}{1.5}$	32,000 min ⁻¹
Spindle Accuracy	Collet	Max. power	Weight
Within 3 μm	CHSS Group (ø1.0 ~ ø3.175mm)	275w	605g
Standard Accessories	Collet : ø3.0mm (CHSS-3.0) / Wrench (7×5.1) · (8×6.1) : 1pc. each		
Options	Collet (CHSS Group) : ø1.0 ~ ø3.175mm p.51 Motor cord : Length 3m (1778), 4m (1768), 6m (1767), 8m (1766)		



※ Joint type motor cord is necessary.

