




工具材料 コーティング 直径許容差 先端角 ねじれ角 直径範囲

●鋼、ステンレス鋼、アルミの深い穴や深い位置の穴あけに適したコーティングロングドリルです。

This is general coated drills for deep holes.



3mm 以上はタンク付き

オーダ方法

GLD 直径 × 全長

単位 (Unit) : mm

直径 Dc	全長 L	溝長 ℓ	在庫 Stock
1.0	100	50	
1.0	150	60	
1.0	200	75	
1.05	100	50	
1.05	150	60	
1.1	100	50	
1.1	150	60	
1.1	200	75	
1.15	100	50	
1.15	150	60	
1.2	100	50	
1.2	150	60	
1.2	200	75	
1.25	100	50	
1.25	150	60	
1.3	100	50	
1.3	150	60	
1.3	200	75	
1.35	100	50	
1.35	150	60	
1.4	100	50	
1.4	150	60	
1.4	200	75	
1.45	100	50	
1.45	150	60	
1.5	100	50	
1.5	150	60	
1.5	200	75	
1.55	100	50	
1.55	150	60	
1.6	100	50	
1.6	150	60	
1.6	200	80	
1.65	100	50	
1.65	150	60	
1.7	100	50	
1.7	150	60	
1.7	200	80	
1.75	100	50	
1.75	150	60	
1.8	100	50	
1.8	150	60	
1.8	200	80	
1.85	100	50	
1.85	150	60	
1.9	100	50	
1.9	150	60	
1.9	200	80	
1.95	100	50	
1.95	150	60	
2.0	100	50	
2.0	125	65	
2.0	150	80	
2.0	200	100	
2.0	300	120	
2.05	100	50	
2.05	150	80	
2.1	100	50	
2.1	125	65	
2.1	150	80	
2.1	200	100	
2.15	100	50	
2.15	150	80	
2.2	100	50	
2.2	125	65	
2.2	150	80	
2.2	200	80	
2.25	100	50	
2.25	150	80	
2.3	100	50	

直径 Dc	全長 L	溝長 ℓ	在庫 Stock
2.3	125	65	
2.3	150	80	
2.3	200	100	
2.35	100	50	
2.35	150	80	
2.4	100	50	
2.4	125	65	
2.4	150	80	
2.4	200	80	
2.45	100	50	
2.45	150	80	
2.5	100	50	
2.5	125	65	
2.5	150	80	
2.5	200	80	
2.5	200	90	
2.5	250	100	
2.5	300	120	
2.55	100	60	
2.55	150	80	
2.6	100	60	
2.6	125	65	
2.6	150	80	
2.6	200	105	
2.65	100	60	
2.65	150	80	
2.7	100	60	
2.7	125	65	
2.7	150	80	
2.7	200	105	
2.75	100	60	
2.75	150	80	
2.8	100	60	
2.8	125	65	
2.8	150	80	
2.8	200	105	
2.85	100	60	
2.85	150	80	
2.9	100	60	
2.9	125	65	
2.9	150	80	
2.9	200	105	
2.95	100	60	
2.95	150	80	
3.0	100	60	
3.0	125	70	
3.0	150	80	
3.0	200	105	
3.0	200	125	
3.0	250	150	
3.0	300	175	
3.0	400	200	
3.05	100	60	
3.05	150	85	
3.1	100	60	
3.1	125	70	
3.1	150	85	
3.1	200	125	
3.1	250	150	
3.1	300	175	
3.15	100	60	
3.15	150	85	
3.2	100	60	
3.2	125	70	
3.2	150	85	
3.2	200	125	
3.2	250	150	
3.2	300	175	
3.25	100	60	
3.25	150	85	

直径 Dc	全長 L	溝長 ℓ	在庫 Stock
3.3	100	60	
3.3	125	70	
3.3	150	85	
3.3	200	125	
3.3	250	150	
3.3	300	175	
3.35	100	60	
3.35	150	85	
3.4	100	60	
3.4	125	70	
3.4	150	85	
3.4	200	125	
3.4	250	150	
3.4	300	175	
3.45	100	60	
3.45	150	85	
3.5	100	60	
3.5	125	75	
3.5	150	85	
3.5	200	110	
3.5	200	125	
3.5	250	150	
3.5	300	175	
3.5	350	210	
3.5	400	250	
3.55	100	60	
3.55	150	90	
3.6	100	60	
3.6	125	75	
3.6	150	90	
3.6	200	125	
3.6	250	150	
3.6	300	175	
3.65	100	60	
3.65	150	90	
3.7	100	60	
3.7	125	75	
3.7	150	90	
3.7	200	125	
3.7	250	150	
3.7	300	175	
3.75	100	60	
3.75	150	90	
3.8	100	60	
3.8	125	75	
3.8	150	90	
3.8	200	125	
3.8	250	150	
3.8	300	175	
3.85	100	60	
3.85	150	90	
3.9	100	60	
3.9	125	75	
3.9	150	90	
3.9	200	125	
3.9	250	150	
3.9	300	175	
3.95	100	60	
3.95	150	90	
4.0	100	60	
4.0	125	75	
4.0	150	90	
4.0	200	120	
4.0	200	125	
4.0	250	150	
4.0	300	175	
4.0	350	210	
4.0	400	260	
4.05	150	90	
4.1	100	60	
4.1	125	75	

直径 Dc	全長 L	溝長 ℓ	在庫 Stock
4.1	150	90	
4.1	200	125	
4.1	250	150	
4.1	300	175	
4.15	150	90	
4.2	100	60	
4.2	125	75	
4.2	150	90	
4.2	200	125	
4.2	250	150	
4.2	300	175	
4.25	150	90	
4.3	100	60	
4.3	125	75	
4.3	150	90	
4.3	200	125	
4.3	250	150	
4.3	300	175	
4.35	150	90	
4.4	100	60	
4.4	125	75	
4.4	150	90	
4.4	200	125	
4.4	250	150	
4.4	300	175	
4.45	150	90	
4.5	100	60	
4.5	125	75	
4.5	150	90	
4.5	200	120	
4.5	200	125	
4.5	250	150	
4.5	300	175	
4.5	350	210	
4.5	400	260	
4.55	150	100	
4.6	100	60	
4.6	125	75	
4.6	150	100	
4.6	200	125	
4.6	250	150	
4.6	300	175	
4.65	150	100	
4.7	100	60	
4.7	125	75	
4.7	150	100	
4.7	200	125	
4.7	250	150	
4.7	300	175	
4.75	150	100	
4.8	100	60	
4.8	125	75	
4.8	150	100	
4.8	200	125	
4.8	250	150	
4.8	300	175	
4.85	150	100	
4.9	100	60	
4.9	125	75	
4.9	150	100	
4.9	200	125	
4.9	250	150	
4.9	300	175	
4.95	150	100	
5.0	125	80	
5.0	150	110	
5.0	200	125	
5.0	250	150	
5.0	300	175	
5.0	350	210	
5.0	400	260	

□は特定代理店在庫品です。

□: Available for Japan customers only.

3mm 以上はタンク付きです。タンク部の詳細は G-44 のタイプ 1 を参照ください。