

●標準寸法では、突出し長さが不足するような場合に使用します。


This tap is used when a standard N Point Tap is too short.



LIST 6908

オーダ方法

NPOL 記号 × 全長



単位 (Unit) : mm / 円 (¥)

記号 Code No.	全長 L	呼び Thread Size	等級 TAP Limit		食付 (P) Lc (P)	ねじ長 ℓ	溝数 Flutes	シャンク径 Ds	首下長さ Ln	形式 Type	在庫 Stock	参考価格 Price										
3M0.5R	100	M3 × 0.5	REG	P2	5	11	3	4.0	18	1	●	2,430										
3M0.5R	120											2,710										
3M0.5R	150											4,660										
4M0.7R	100	M4 × 0.7	REG	P2	5	13	3	5.0	20	1	●	2,190										
4M0.7R	120											2,710										
4M0.7R	150											4,660										
5M0.8R	100	M5 × 0.8	REG	P2	5	16	3	5.5	22	1	●	1,880										
5M0.8R	120											2,490										
5M0.8R	150											3,370										
6M1R	100	M6 × 1	REG	P2	5	19	3	6.0	27	1	●	1,630										
6M1R	120											2,210										
6M1R	150											2,900										
8M1.25R	100	M8 × 1.25	REG	P3	5	22	3	6.2	34	2	●	2,070										
8M1.25R	120											2,710										
8M1.25R	150											3,580										
10M1.5R	100	M10 × 1.5	REG	P3	5	24	3	7.0	39	2	●	2,710										
10M1.5R	120											3,270										
10M1.5R	150											4,170										
10M1.25R	100	M10 × 1.25	REG	P3	5	24	3	7.0	39	2	●	2,710										
10M1.25R	120											3,270										
10M1.25R	150											4,410										
12M1.75R	150	M12 × 1.75	REG	P3	5	29	3	8.5	45	3	●	5,320										
12M1.75R	200											6,600										
12M1.5R	150											M12 × 1.5	REG	P3	5	29	3	8.5	45	3	●	5,620
12M1.25R	150	REG	P3	5	29	3	8.5	45	3	●	5,620											
14M2R	150	M14 × 2	REG	P3	5	30	3	10.5	49	3	●	7,010										
14M2R	200											8,170										
14M1.5R	150	M14 × 1.5	REG	P3	5	30	3	10.5	49	3	●	7,010										
16M2R	150											M16 × 2	REG	P3	5	32	3	12.5	52	3	●	7,520
16M2R	200	9,860																				
16M1.5R	150	M16 × 1.5	REG	P3	5	32	3	12.5	52	3	●	7,520										
16M1.5R	200											9,860										
18M2.5R	150	M18 × 2.5	REG	P3	5	37	3	14.0	56	3	●	10,200										
18M2.5R	200											12,900										
18M1.5R	150											M18 × 1.5	REG	P3	5	37	3	14.0	56	3	●	10,200
18M1.5R	200	12,900																				
20M2.5R	150	M20 × 2.5	REG	P3	5	37	3	15.0	57	3	●	12,900										
20M2.5R	200											16,200										
20M1.5R	150											M20 × 1.5	REG	P3	5	37	3	15.0	57	3	●	12,900
20M1.5R	200	16,200																				
22M2.5R	200	M22 × 2.5	REG	P3	5	38	3	17.0	62	3	●	17,500										
22M1.5R	150											M22 × 1.5	REG	P3	5	38	3	17.0	62	3	●	14,400
22M1.5R	200																					17,500
24M3R	150	M24 × 3	REG	P4	5	45	3	19.0	67	3	●	16,800										
24M3R	200											20,200										
24M1.5R	150											M24 × 1.5	REG	P3	5	45	3	19.0	67	3	●	16,800
24M1.5R	200	20,200																				

● : 標準在庫品 Stocked items

・形式 1 ~ 2 は突出しセンタ Type 1 ~ 2 with External Centre

・シャンク四角部寸法 K, Lk は B-44 を参照 Refer to B-44 for the square portion size of shank