




Please maintain not to exceed speed limit.

90° Angle Spindle	O.D.	Rotating speed at the cutting tool	Reduction Ratio	Allowable motor speed for the spindle	Spindle Accuracy	Collet	Weight
<b>RAS-151E</b>	ø30mm	<b>7,200</b> min <sup>-1</sup> *	<b>1/2.67</b>	<b>19,000</b> min <sup>-1</sup> (Using AM-3020R)	Within 2 μm	<b>ø0.5~ø6.35</b> mm (CHK Group)	<b>413</b> g

※ Maximum rotating speed at the cutting tool for the reduction ratio.

DXF-data



Code No. **7840** Model **RAS-151E**


< Standard Accessories >

- Collet Nut (K-265)
- Wrench (12 x 14): 2pcs., (22 x 27): 1pc.

< Options >

Collet (CHK Group) : ø0.5~ø6.35mm See Page 30 for details


※ Collet is sold separately.



90° Angle Spindle	O.D.	Rotating speed at the cutting tool	Reduction Ratio	Allowable motor speed for the spindle	Collet	Weight
<b>RA-151E</b>	ø30mm	<b>7,200</b> min <sup>-1</sup> *	<b>1/2.67</b>	<b>19,000</b> min <sup>-1</sup> (Using AM-3020R)	<b>ø0.8~ø3.175</b> mm (CH8 Group)	<b>385</b> g

※ Maximum rotating speed at the cutting tool for the reduction ratio.

DXF-data




Code No. **1505** Model **RA-151E**

< Standard Accessories >

- Collet : ø3.0mm (CH8-3.0)
- Wrench (7 x 5.5), (8 x 5), (22 x 27) : 1pc. each

< Options >


Collet (CH8 Group) : ø0.8~ø3.175mm See Page 30 for details



90° Angle Spindle	O.D.	Rotating speed at the cutting tool	Reduction Ratio	Allowable motor speed for the spindle	Collet	Weight
<b>RA-271E</b>	ø30mm	<b>12,700</b> min <sup>-1</sup> *	<b>1/1.5</b>	<b>19,000</b> min <sup>-1</sup> (Using AM-3020R)	<b>ø0.8~ø3.175</b> mm (CHS Group)	<b>240</b> g

※ Maximum rotating speed at the cutting tool for the reduction ratio.

DXF-data



Code No. **1506** Model **RA-271E**

< Standard Accessories >

- Collet : ø3.0mm (CHS-3.0)
- Wrench (7 x 5.1), (8 x 5), (22 x 27) : 1pc. each

< Options >

Collet (CHS Group) : ø0.8~ø3.175mm See Page 30 for details

