


# LEFT-HAND VERNIER CALIPERS




## DIMENSIONS

Units : mm

**USE** • For outside diameter, inside diameter, step and depth measurement


### FEATURES

- Designed specially for left-handed use
- Made of stainless steel
- Satin finish




Order No.	Model No.	Measuring Range (mm)	Graduation (mm)	Accuracy (mm)	Depth Bar	Weight
151321	THL-150	150	0.05	± 0.05	Yes	150g

# DIAL CALIPERS/ DIAL CALIPERS WITH CARBIDE TIPPED MEASURING FACE




DVC-15 II



DVC-15W, DVC-20W, DVC-30W are carbide-tipped for outside & inside measurement

## DIMENSIONS



Units : mm

**USE** • For outside diameter, inside diameter, step and depth measurement

### FEATURES

- Slider displacement is amplified by rack-and-pinion mechanism and indicated on the dial
- Available with carbide-tipped measuring faces( DVC-15W ~ 30W)
- Made of stainless steel
- Satin finish

Model No.	A	B	C	D	E	F	G	H
DVC-15 II	236	77	16	40	58	21	16	38
DVC-20 II	285	90	19	50	59	24	16	38
DVC-30 II	400	103	18	60	59	25	17	45
DVC-15W	236	77	16	40	58	21	16	38
DVC-20W	285	90	19	50	59	24	16	38
DVC-30W	400	103	18	60	59	25	17	45

Order No.	Model No.	Measuring Range (mm)	Graduation (mm)	Accuracy (mm)	Depth Bar	Indicator 1 revolution (mm)	Weight	Note
151351	DVC-15 II	150	0.02	± 0.03	Yes	2	200g	—
151352	DVC-20 II	200	0.02	± 0.03	Yes	2	240g	—
151353	DVC-30 II	300	0.02	± 0.04	Yes	2	360g	—
151361	DVC-15W	150	0.02	± 0.03	Yes	2	200g	Carbide-tipped measuring faces
151362	DVC-20W	200	0.02	± 0.03	Yes	2	240g	Carbide-tipped measuring faces
151363	DVC-30W	300	0.02	± 0.04	Yes	2	370g	Carbide-tipped measuring faces