



Saw · File

- Remarkable cutting speed by its dual action design.
- Rubber grip for operator comfort.



Saw · AS-22A

2 pcs of 32 teeth saws included.

■ Saws for AS-22A

	24 teeth for aluminum	32 teeth for aluminum
AS-22A	 No.24906130	 No.24906133







package



File · AS-22AF

4 files, 1 each of all kinds included.

■ Files for AS-22AF

AS-22AF	Flat file	Semi-round file
	 No.24906196	 No.24906183
	Round file	Triangle file
	 No.24906162	 No.24906166

Model	Code	Max. sheet thickness mild steel		Free frequency per minute	Overall length		Weight		Air inlet thread	Hose size		Average air consumption	
		mm	in		mm	in	kg	lb		Rc	mm	in	m ³ /min
AS-22A	10791	1.5	1/16	10000	212	8 ³ / ₈	0.6	1.3	1/4	6.3	1/4	0.25	8.8
AS-22AF	10810	-	-	6500	203	8	0.6	1.3	1/4	6.3	1/4	0.11	3.9



Dia Cutter

- Designed for speedy cutting and trimming work.
- Many applications including automotive repairing, cement, duralumin, removing burr from casting, window frame, sheet metal, and fiber glass manufacturing.



DAC-11



1 cutter included.

Model	Code	Max. sheet thickness mild steel		Max. free speed	Overall length		Weight		Air inlet thread	Hose size		Average air consumption	
		mm	in		mm	in	kg	lb		Rc	mm	in	m ³ /min
DAC-11	10225	54x1.3x10	2 ¹ / ₈ x ³ / ₆₄ x ³ / ₈	13000	298	11 ³ / ₄	1.7	3.7	1/4	6.3	1/4	0.45	15.9