





# INSPECTION MIRROR WITH LED LIGHT




## FEATURES

- Inspection around and behind obstacles and in poorly lit areas
- LED light for high visibility
- Inspection mirror : 2 pcs (  $\phi$  20mm,  $\phi$  30mm )
- Power : Two "AA" size batteries included for testing
- Stalk : Stainless steel
- Grip : Brass ( Silver finish )

## DIMENSIONS

Units : mm



Order No.	Model No.	Operating Temperature	Luminance	Weight
011105	LM-340	- 10 ~ 40°C	10000mcd	126g


# INSPECTION MIRROR WITH LIGHT

## M type



## DIMENSIONS

Units : mm



## FEATURES

- Inspection solution for dark tight spaces
- Flexible stem can be bent to any angle
- Mirror can be removed for use as flexible light
- Power : two "AA" size batteries included for testing

Order No.	Model No.	Ball nipple bulb	Weight
011100	LMF-M	2.2V 0.25A	200g


# INSPECTION MIRROR WITH LIGHT

## L type



## DIMENSIONS

Units : mm



## FEATURES

- Inspection solution for dark tight spaces
- Brass ( Silver finish )
- Telescoping stalk with flexible end mirror angle adjustable for any requirement
- $\phi$  100 planar mirror
- Krypton bulb for high intensity light
- Power : two "AA" size batteries included for testing

Order No.	Model No.	Krypton bulb	Weight
011103	LMF-L	2.5V 0.75A	500g