

# SCALING

Pneumatic Chipping Hammer

## AIR CHIPPER

### Removes weld spatter quickly and easily

- Ideal tool for quickly and efficiently removing weld spatter, rust and other debris from most surfaces
- Compact, heavy-duty construction for tough industrial applications
- Easy one-touch chisel installation and removal – NO tools required
- Idle protection system, helps prevent accidental start-up “ACH-16” only

Model **ACH-16** 



Model **CH-24** 



Specifications		ACH-16	CH-24
Model			
Air Pressure	MPa (kgf/cm <sup>2</sup> )		0.6 (6)
Air Consumption (No-load)	m <sup>3</sup> /min	0.15	0.2
Strokes per Minute	min <sup>-1</sup>	6000	4000
Shank Size	mm	10.5 Round	12.7 Square
Inlet Size			Rc 3/8
Mass (Weight)	kg	0.9	1.7
Accessories Included		<ul style="list-style-type: none"> <li>• TQ03431 Flat Chisel (Installed)</li> <li>• Bushing R 3/8 x NPT 3/8</li> <li>• Hose Nipple R 3/8 x 3/8</li> </ul>	<ul style="list-style-type: none"> <li>• TP15166 Curved Flat Chisel (Installed)</li> <li>• Bushing R 3/8 x NPT 3/8</li> <li>• Hose Nipple R 3/8 x 3/8</li> </ul>

#### Optional Chisels for Air Chipper ACH-16

Ref. No.	PN	Description	Sales Unit
1	TQ03431	Flat Chisel 20 x 120	1 piece
2	TQ03452	Flat Chisel 20 x 180	
3	TQ03453	Curved Flat Chisel 20 x 120	
4	TQ03549	Flat Chisel 11 x 120	

#### Optional Chisels for Air Chipper CH-24

Ref. No.	PN	Description	Sales Unit
5	TP15233	Flat Chisel 25 x 155	1 piece
6	TP15234	Straight Flat Chisel 12.7 x 165	
7	TP15166	Curved Flat Chisel 25 x 155	

