


Specify Part No. by required size.  
(e.g.) Diameter is 5.556mm (7/32 in).

**ABG - 55**  
Part No.



Part No.	Diameter $\phi D$				Sphericity
	inch	mm	Tolerance	Lot diameter variation (max)	max
<b>ABG-31</b>	1/8	3.175	$\pm 50\mu\text{m}$	10 $\mu\text{m}$	5 $\mu\text{m}$
<b>ABG-39</b>	5/32	3.969	$\pm 50\mu\text{m}$	10 $\mu\text{m}$	5 $\mu\text{m}$
<b>ABG-55</b>	7/32	5.556	$\pm 50\mu\text{m}$	10 $\mu\text{m}$	5 $\mu\text{m}$
<b>ABG-71</b>	9/32	7.144	$\pm 50\mu\text{m}$	15 $\mu\text{m}$	7 $\mu\text{m}$
<b>ABG-95</b>	3/8	9.525	$\pm 50\mu\text{m}$	15 $\mu\text{m}$	7 $\mu\text{m}$
<b>ABG-127</b>	1/2	12.700	$\pm 50\mu\text{m}$	15 $\mu\text{m}$	7 $\mu\text{m}$

The dimensional tolerances are the values measured at +25°C.