

25M

Oiles 250-07 (425-07) Bar Stock



Specify Part No. by required diameter.
(e.g.) Diameter is 40mm.

25M - 40

Part No.




- The 250-07 bar stock may be used as the 425-07 (for underwater use) if it is machined and process with paraffin then.

Part No.	Diameter		Thickness
	φD	Tolerance	L
25M-30	30	+2.0 +1.0	500
25M-40	40	+2.0 +1.0	500
25M-50	50	+2.5 +1.0	500
25M-60	60	+2.5 +1.0	500

25P


Oiles 250-07 (425-07) Plate Material



Specify Part No. by required width and thickness.
(e.g.) Wide is 250mm, thickness is 11mm.

25P - 2511

Part No.



- The 250-07 plate material may be used as the 425-07 (for underwater use) if it is machined and processed with paraffin then.

Part No.	Width		Thickness		Length
	W	Tolerance	T	Tolerance	L
25P-2506	250	+10.0 +1.0	6	+2.0 0	500
25P-2511	250	+10.0 +1.0	11	+2.0 0	500
25P-2521	250	+10.0 +1.0	21	+2.0 0	500