

# Specifications

**DXF data** DXF files are available on our website

Order by Code No.

## EM30-S6000

Code No. **7903** Model **EM30-S6000**




O.D.	Max. rpm	Spindle Accuracy	Collet	Max. power	Weight
Ø30mm	60,000min <sup>-1</sup>	Within 1μm	<b>CHK Group</b> (ø0.5 ~ ø6.35mm)	<b>350w</b>	<b>575g</b>

**Standard Accessories** Collet nut (K-265) / Wrench (12×14) : 2pcs.

Options
Collet (CHK Group) : ø0.5 ~ ø6.35mm <b>p.51</b>
Motor cord : Length 4m (1748), 6m (1749), 8m (1750) ※Angle type is also available
Metal Saw Arbor (KCH-03) : ød (I.D.) × under ø30mm (O.D.) /
Grindstone Arbor (AGM-03) : Grindstone I.D. ø5.0mm
Grindstone Flange (EGF-19) : for grindstone I.D. ø19.05×O.D. ø40×7mm

※ Collet is sold separately.



## EM25-S6000

Code No. **7858** Model **EM25-S6000**




O.D.	Max. rpm	Spindle Accuracy	Collet	Max. power	Weight
Ø25mm	60,000min <sup>-1</sup>	Within 1μm	<b>CHA Group</b> (ø0.5 ~ ø4.0mm)	<b>250w</b>	<b>375g</b>

**Standard Accessories** Collet nut (CHN-A) / Wrench (8×5) · (9×11) : 1pc. each

Options
Collet (CHA Group) : ø0.5 ~ ø4.0mm <b>p.51</b>
Motor cord : Length 4m (1748), 6m (1749), 8m (1750) ※Angle type is also available

※ Collet is sold separately.



## EM20-S6000

Code No. **7860** Model **EM20-S6000**



O.D.	Max. rpm	Spindle Accuracy	Collet	Max. power	Weight
Ø20mm	60,000min <sup>-1</sup>	Within 1μm	<b>CHA Group</b> (ø0.5 ~ ø4.0mm)	<b>250w</b>	<b>230g</b>

**Standard Accessories** Collet nut (CHN-A) / Wrench (8×5) · (9×11) : 1pc. each

Options
Collet (CHA Group) : ø0.5 ~ ø4.0mm <b>p.51</b>
Motor cord : Length 4m (1748), 6m (1749), 8m (1750) ※Angle type is also available

※ Collet is sold separately.

