



ヘルールレジュース／ヘルール偏心レジュース
Reducer(Eccentric) both end Ferrule/Reducer(Eccentric) both end Ferrule

ヘルールレジュース

Reducer (Concentric) both end Ferrule


Type RDC-2C



ヘルール偏心レジュース

Reducer (Eccentric) both end Ferrule

Type RDE-2C




Nom.size	ID1	ID2	L		Mass kg
			Concentric	Eccentric	
※ 1.25 ^S ×1.0 ^S	29.4	23	45	105.5	0.15
※ 1.5 ^S ×1.0 ^S	35.7	23	45	110	0.19
※ 1.5 ^S ×1.25 ^S	35.7	29.4	45	105.5	0.14
※ 2.0 ^S ×1.0 ^S	47.8	23	45	110	0.24
※ 2.0 ^S ×1.25 ^S	47.8	29.4	45	105.5	0.19
※ 2.0 ^S ×1.5 ^S	47.8	35.7	45	110	0.17
2.5 ^S ×1.0 ^S	59.5	23	110	110	0.38
2.5 ^S ×1.25 ^S	59.5	29.4	105.5	105.5	0.36
2.5 ^S ×1.5 ^S	59.5	35.7	110	110	0.3
2.5 ^S ×2.0 ^S	59.5	47.8	110	110	0.35
3.0 ^S ×1.5 ^S	72.3	35.7	110	110	0.46
3.0 ^S ×2.0 ^S	72.3	47.8	110	110	0.39
3.0 ^S ×2.5 ^S	72.3	59.5	110	110	0.41
3.5 ^S ×2.0 ^S	85.1	47.8	110	110	0.55
3.5 ^S ×2.5 ^S	85.1	59.5	110	110	0.53
3.5 ^S ×3.0 ^S	85.1	72.3	110	110	0.54
4.0 ^S ×2.0 ^S	97.6	47.8	151.5	151.5	0.81
4.0 ^S ×2.5 ^S	97.6	59.5	151.5	151.5	0.84
4.0 ^S ×3.0 ^S	97.6	72.3	151.5	151.5	0.95
4.0 ^S ×3.5 ^S	97.6	85.1	151.5	151.5	0.81

※Option
(偏心レジュースと同全長)
ヘルールレジュース(ロング)
Type RDL-2C

ヘルールレジュース

Reducer (Concentric) both end Ferrule


Type RDC-2C



ヘルール偏心レジュース

Reducer (Eccentric) both end Ferrule

Type RDE-2C



※すべて SUS316L
All SUS316L

Nom.size	ID1	ID2	L1	L2	Mass kg
10A×8A	14	10.5	45	72.1	0.08
15A×8A	17.5	10.5	45	72.1	0.08
15A×10A	17.5	14	45	72.1	0.07
1.0 ^S ×8A	23	10.5	45	76.6	0.14
1.0 ^S ×10A	23	14	45	76.6	0.13
1.0 ^S ×15A	23	17.5	45	76.6	0.12
1.5 ^S ×8A	35.7	10.5	45	76.6	0.12
1.5 ^S ×10A	35.7	14	45	76.6	0.11
1.5 ^S ×15A	35.7	17.5	45	76.6	0.11