




Straight Shank Jobber Drills



Codes
101, 102

Properties		
M INCH	DIN 338	HSS
	TYPE N	
	30°	BLUE FINISH
	STANDARD POINT sizes below 3.0 mm	
	SPLIT POINT 3.0 mm and above	



JOBBER DRILL SETS IN METAL CASES

Size Range	No. of drills	Code
1 - 7 x 0.5	13	1060020
1 - 10 x 1	10	1060025
1 - 10 x 0.5	19	1060030
1 - 13 x 1	13	1060035
1 - 13 x 0.5	25	1060040
1 - 6 x 0.1	51	1060070
6 - 10 x 0.1	41	1060080
1/16" - 1/2" x 1/64"	29	1070030
1/16" - 1/2" x 1/32"	15	1070040



COUNTER DISPENSERS

Size Range	Code
10 each of: 1, 2, 3, 3.2, 4, 4.8, 5, 6, 6.5, 7, 8, 9	
5 each of: 1.2, 1.5, 1.8, 2.2, 2.5, 2.8, 3.5, 3.8, 4.2, 4.5, 5.2, 5.5, 5.8, 6.2, 7.5, 8.5, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13	1019000
with Counter Dispenser	
Counter Dispenser only	1019001

d		l ₂	l ₁	Code
mm	inch			
0.3		3	19	1010030
0.35		4	19	1010035
0.397	1/64	5	20	1020040
0.4		5	20	1010040
0.45		5	20	1010045
0.5		6	22	1010050
0.55		7	24	1010055
0.6		7	24	1010060
0.62		8	26	1010062
0.7		9	28	1010070
0.75		9	28	1010075
0.794	1/32	10	30	1020079
0.8		10	30	1010080

d		l ₂	l ₁	Code
mm	inch			
0.88		11	32	1010088
0.9		11	32	1010090
0.92		11	32	1010092
1		12	34	1010100
1.05		12	34	1010105
1.1		14	36	1010110
1.15		14	36	1010115
1.191	3/64	16	38	1020119
1.2		16	38	1010120
1.25		16	38	1010125
1.3		16	38	1010130
1.35		18	40	1010135
1.4		18	40	1010140
1.45		18	40	1010145
1.5		18	40	1010150
1.55		20	43	1010155
1.587	1/16	20	43	1020159
1.6		20	43	1010160
1.65		20	43	1010165
1.7		20	43	1010170
1.75		22	46	1010175
1.8		22	46	1010180
1.85		22	46	1010185
1.9		22	46	1010190
1.95		24	49	1010195
1.984	5/64	24	49	1020198
2		24	49	1010200
2.05		24	49	1010205
2.1		24	49	1010210
2.15		27	53	1010215
2.2		27	53	1010220
2.25		27	53	1010225
2.3		27	53	1010230
2.35		27	53	1010235
2.381	3/32	30	57	1020238
2.4		30	57	1010240
2.45		30	57	1010245
2.5		30	57	1010250
2.55		30	57	1010255
2.6		30	57	1010260
2.65		30	57	1010265
2.7		33	61	1010270
2.75		33	61	1010275
2.778	7/64	33	61	1020278
2.8		33	61	1010280
2.85		33	61	1010285
2.9		33	61	1010290
2.95		33	61	1010295
3		33	61	1010300
3.1		36	65	1010310



STRAIGHT SHANK DRILLS

Continued on next page...