

54B


オイルレスサーメットMブッシュ





適用する内径、外径、長さから Parts No. を選んでください。
 (例)内径12mm、外径18mm、長さ10mmの場合

54B - 121810

Parts No. でご指示ください。



●面取りについては、寸法図の表記以外に
 以下形状の場合もあります。(両端共)



内径		外径		長さ L 公差 $\begin{smallmatrix} 0 \\ -0.1 \\ -0.3 \end{smallmatrix}$											圧入後 内径 公差 (参考値)
φd	公差	φD	公差	3	4	5	6	8	10	15	20	25	30	40	
3	+0.024 +0.014	6	+0.027 +0.015	030603		030605									+0.017 +0.007
4	+0.032 +0.020	7	+0.034 +0.019		040704	040705	040706								+0.023 +0.011
5	+0.032 +0.020	8	+0.034 +0.019			050805	050806	050808							+0.023 +0.011
6	+0.032 +0.020	10	+0.034 +0.019			061005	061006	061008	061010						+0.023 +0.011
8	+0.040 +0.025	12	+0.041 +0.023				081206	081208	081210	081215					+0.029 +0.014
10	+0.040 +0.025	16	+0.041 +0.023				101606	101608	101610	101615	101620				+0.029 +0.014
12	+0.050 +0.032	18	+0.041 +0.023					121808	121810	121815	121820				+0.039 +0.021
14	+0.050 +0.032	20	+0.049 +0.028						142010	142015	142020				+0.036 +0.018
15	+0.050 +0.032	21	+0.049 +0.028						152110	152115	152120	152125			+0.036 +0.018
16	+0.050 +0.032	22	+0.049 +0.028						162210	162215	162220	162225			+0.036 +0.018
18	+0.050 +0.032	24	+0.049 +0.028						182410	182415	182420	182425	182430		+0.036 +0.018
20	+0.061 +0.040	28	+0.049 +0.028							202815	202820		202830		+0.047 +0.026
25	+0.061 +0.040	35	+0.059 +0.034								253520	253525	253530		+0.044 +0.023
30	+0.061 +0.040	40	+0.059 +0.034								304020	304025	304030	304040	+0.044 +0.023

※圧入後内径公差は参考値です。