




# LEVER COUPLINGS アルミニウム

## OZ-A メスネジ型アダプター

### ADAPTER FEMALE THREAD




呼び径	mm	15	20	25	32	40	50	65	80	100	125	150	200
	inch	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6	
M		1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6	
ΦD		32	32	37	46	53	63	76	92	120		176	
ΦE		16	22	24	29	36	46	56	72	97		150	
h		26	28	34	40	42	48	49	51	53		58	
H		38	38	47	55	59	63	85	70	78		86	
K		34	34	41	48	56	67	85	98	128		192	

単位:mm

## OZ-F オスネジ型アダプター

### ADAPTER MALE THREAD




呼び径	mm	15	20	25	32	40	50	65	80	100	125	150
	inch	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6
M		1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6
ΦD		32	32	37	46	53	63	76	92	120		176
ΦE		16	21	24	29	36	46	56	72	97		150
h1		28	28	34	40	43	46	49	51	53		60
h2		20	20	23	24	24	26	31	32	36		43
H		58	58	70	79	83	88	99	102	114		129
K		34	34	41	48	56	67	88	96	127		192

単位:mm

## OZ-E ホースシャンクアダプター

### ADAPTER HOSE SHANK




呼び径	mm	20	25	32	40	50	65	80	100	125	150	200
	inch	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6	
ΦD		32	37	46	53	63	76	92	120		176	
ΦF		11	19	25	31	42	55	67	92		142	
ΦG		19	25	32	38	50	63	75	101		152	
ΦI		21	27	34	40	52	65	79	105		155	
h1		27	34	40	40	47	50	51	53		78	
h2		51	60	64	66	77	95	102	110		143	
H		89	104	115	117	137	159	167	178		221	

単位:mm

## OZ-EP プラスチックホース用アダプター

### ADAPTER HOSE SHANK



呼び径	mm	40	50	65	80	100	125	150
	inch	1 1/2	2	2 1/2	3	4		6
ΦD		53	63	76	92	120		176
ΦE		36	45	56	71	97		148
ΦF		31	43	55	67	92		142
ΦG		36	49	62	75	101		149
ΦI		38	51	64	77	103		152
h1		41	46	50	51	54		60
h2		72	83	90	104	113		143
L		15	15	15	15	15		15
N		4	5	4	5	6		5
H		123	143	154	170	182		221

単位:mm