


AMM Oiles Aramid M Bar Stock



Specify Part No. by required diameter.
(e.g.) Diameter is 20mm.


AMM - 20
Part No.



Part No.	Diameter		Length
	φD	Tolerance	L
AMM-08	8	+2.5 0	100
AMM-10	10	+2.5 0	100
AMM-15	15	+2.5 0	100


Part No.	Diameter		Length
	φD	Tolerance	L
AMM-20	20	+2.5 0	200
AMM-30	30	+2.5 0	200
AMM-40	40	+2.5 0	200
AMM-50	50	+2.5 0	200
AMM-60	60	+2.5 0	200

AMS Oiles Aramid M Bushings



Specify Part No. by required I.D. and O.D.
(e.g.) I.D. is 20mm and O.D. is 60mm.

AMS - 2060
Part No.



Part No.	I.D.		O.D.		Length
	φd	Tolerance	φD	Tolerance	
AMS-1030	10	-1.0 -3.0	30	+3.0 +1.0	35
AMS-2060	20	-1.0 -3.0	60	+3.0 +1.0	35
AMS-50100	50	-1.0 -3.0	100	+3.0 +1.0	35
AMS-100160	100	-1.0 -3.0	160	+3.0 +1.0	35