


# ST45B

## Ø45mm Bulb Steady/Flashing Tower Lights



- ST45B** Steady
- ST45B-BZ** Built-in Buzzer Steady
- ST45BF** Steady/Flashing
- ST45BF-BZ** Built-in Buzzer Steady/Flashing



### ST45B series

Built-in buzzer output holes formed on the housing of the product.



## ST45B Ø45mm Pole Mount, Bulb Steady/Flashing

Model number	Layer	Voltage	Current	Bulb			Certificates	Weight	Color
				Spec	Standard	Parts no#			
ST45B Steady ST45B-BZ Steady /w built-in buzzer ST45BF Steady/ Flashing ST45BF-BZ Steady/ Flashing /w built-in buzzer	1	AC/DC12V	0.398A	12V5W	G14 9S	1	CE DC only	0.36kg	● R-Red
		AC/DC24V	0.212A	24V5W	G14 9S	2			
		AC110V	0.048A	110V5W	T16x28 9S	3			
		AC220V	0.023A	220V5W	T16x28 9S	4			
	2	AC/DC12V	0.797A	12V5W	G14 9S	1		0.41kg	● R-Red ● G-Green
		AC/DC24V	0.424A	24V5W	G14 9S	2			
		AC110V	0.097A	110V5W	T16x28 9S	3			
		AC220V	0.046A	220V5W	T16x28 9S	4			
	3	AC/DC12V	1.196A	12V5W	G14 9S	1		0.46kg	● R-Red ● A-Amber ● G-Green
		AC/DC24V	0.636A	24V5W	G14 9S	2			
		AC110V	0.146A	110V5W	T16x28 9S	3			
		AC220V	0.070A	220V5W	T16x28 9S	4			
4	AC/DC12V	1.595A	12V5W	G14 9S	1	0.51kg	● R-Red ● A-Amber ● G-Green ● B-Blue		
	AC/DC24V	0.848A	24V5W	G14 9S	2				
	AC110V	0.195A	110V5W	T16x28 9S	3				
	AC220V	0.093A	220V5W	T16x28 9S	4				
5	AC/DC12V	1.994A	12V5W	G14 9S	1	0.56kg	● R-Red ● A-Amber ● G-Green ● B-Blue ● W-White		
	AC/DC24V	1.061A	24V5W	G14 9S	2				
	AC110V	0.244A	110V5W	T16x28 9S	3				
	AC220V	0.116A	220V5W	T16x28 9S	4				

\* Please refer to page 255 ST45MB type for signal/ audible line current.

### Mounting Bracket

Standard	LB18	LW18	QZ18	SZ18	QL18	SL18	QLA18
Steel	Steel	PC	PC	Al	PC	Al	PC

\* Please refer to page 34-39 for detailed dimensions.

### Customization

- Customized pole length available
- 2 buzzer sound types : Both prolonged (beep, beep) and staccato (beep, beep, beep) buzzer output available

### Ordering Specification

<b>ST45B</b>	-	<b>3</b>	-	<b>24</b>	-	<b>RAG</b>	-	<b>LW18</b>
[Model number]		[Layer]		[Voltage]		[Color]		[Mounting bracket]
<ul style="list-style-type: none"> <li>• ST45B</li> <li>• ST45B-BZ</li> <li>• ST45BF</li> <li>• ST45BF-BZ</li> </ul>		<ul style="list-style-type: none"> <li>• 1-1Layer</li> <li>• 2-2Layers</li> <li>• 3-3Layers</li> <li>• 4-4Layers</li> <li>• 5-5Layers</li> </ul>		<ul style="list-style-type: none"> <li>• 12-DC12V</li> <li>• 24-DC24V</li> <li>• 110-AC110V</li> <li>• 220-AC220V</li> </ul>		<ul style="list-style-type: none"> <li>● R-Red</li> <li>● A-Amber</li> <li>● G-Green</li> <li>● B-Blue</li> <li>● W-White</li> </ul>		<ul style="list-style-type: none"> <li>• None</li> <li>• -Standard</li> <li>• Bracket</li> <li>• -LB18</li> <li>• -LW18</li> <li>• -QZ18</li> <li>• -SZ18</li> <li>• -QL18</li> <li>• -SL18</li> <li>• -QLA18</li> </ul>



Warning/Signal/Stackable



Signal & Electric Horn/Speakers



Vessels and Heavy-Duty Equipment



Explosion Proof



Warning Light Bar



Aviation Obstruction Lights



Signal Tower Lights



USB/ETN Signal Tower Lights



Wireless Network System



Electric Horn/Speakers



Industrial LED Lights