

# 溝付きピン

Grooved Pins

欧米では一般的な、相手穴精度を必要としない簡易型ノックピンです。  
溝両側に形成された突起により、締結します。多くの形状があり、用途によって最適なものが選択できます。  
相手穴推奨公差は、呼び径3mmまではH9、呼び径4mm以上はH11です。




溝付きピン C形 DIN 1473

材質 快削鋼

表面処理 呼び径4以上は黒染

仕様・規格・サイズ表 |



呼び寸法 dXL

d	C	f	L																			
			D																			
1.2	h9	0.16	0.6	4	5	6	8															
				1.25	1.25	1.25	1.25															
1.5	h9	0.2	0.8	4	5	6	8	10	12	16	20											
				1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6											
2	h9	0.25	0.9	5	6	8	10	12	16	20	26	30										
				2.15	2.15	2.15	2.15	2.15	2.15	2.15	2.15	2.15	2.15	2.15	2.15							
2.5	h9	0.3	1.2	6	8	10	12	16	20	26	30											
				2.65	2.65	2.65	2.65	2.65	2.65	2.65	2.65											
3	h9	0.4	1.3	6	8	10	12	16	20	26	30											
				3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2											
4	h11	0.5	1.8	8	10	12	16	20	26	30	36	40	45									
				4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25	4.25						
5	h11	0.6	2.0	8	10	12	16	20	26	30	36	40	45									
				5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25	5.25						
6	h11	0.8	2.5	10	12	16	20	26	30	36	40	45	50	55	60							
				6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
8	h11	1.0	2.8	12	16	20	26	30	36	40	45	50	55	60								
				8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3