


Reamers

LMR

ロング刃マシンリーマ
Long Machine Reamers



※食付き角45° 45° Chamfer

- 刃長が豊富
Wide variety of flute lengths
- 深穴加工に最適
Ideal for deep hole work
- MCO材(コバルト高速度鋼)を使用
Uses MCO material (Cobalt high-speed steel)

Endmills

Drills

Countersinks/
Counterbores

Slitting Saws/
Cut-off tools

Cutters

Hand

Machine

Chucking

SPEED
REAMER

Bridge

Taper Pin

Shell

刃長150mm Flute length 150mm

品番 Product No.	寸法 Size					標準価格 Standard price ¥
	刃径 D	シャンク No.	刃長 ℓ	全長 L	刃数 NT	
LMR150X050	5.0	MT1	150	240	6	22,600
LMR150X055	5.5	MT1	150	240	6	22,600
LMR150X060	6.0	MT1	150	240	6	22,600
LMR150X065	6.5	MT1	150	240	6	23,300
LMR150X070	7.0	MT1	150	240	6	23,300
LMR150X075	7.5	MT1	150	240	6	23,300
LMR150X080	8.0	MT1	150	240	6	23,300
LMR150X085	8.5	MT1	150	240	6	25,300
LMR150X090	9.0	MT1	150	240	6	25,300
LMR150X095	9.5	MT1	150	240	6	25,300
LMR150X100	10.0	MT1	150	240	6	25,300
LMR150X105	10.5	MT1	150	240	6	27,200
LMR150X110	11.0	MT1	150	240	6	27,200
LMR150X115	11.5	MT1	150	240	6	28,200
LMR150X120	12.0	MT1	150	240	6	28,200
LMR150X125	12.5	MT1	150	240	6	28,800
LMR150X130	13.0	MT1	150	240	8	28,800
LMR150X135	13.5	MT1	150	240	8	29,700
LMR150X140	14.0	MT1	150	240	8	29,700
LMR150X145	14.5	MT2	150	280	8	31,300
LMR150X150	15.0	MT2	150	280	8	31,300
LMR150X155	15.5	MT2	150	280	8	32,600
LMR150X160	16.0	MT2	150	280	8	32,600

刃長200mm Flute length 200mm

品番 Product No.	寸法 Size					標準価格 Standard price ¥
	刃径 D	シャンク No.	刃長 ℓ	全長 L	刃数 NT	
LMR200X080	8.0	MT1	200	290	6	27,400
LMR200X085	8.5	MT1	200	290	6	27,400
LMR200X090	9.0	MT1	200	290	6	27,400
LMR200X095	9.5	MT1	200	290	6	27,400
LMR200X100	10.0	MT1	200	290	6	27,400
LMR200X105	10.5	MT1	200	290	6	28,900

品番 Product No.	寸法 Size					標準価格 Standard price ¥
	刃径 D	シャンク No.	刃長 ℓ	全長 L	刃数 NT	
LMR200X110	11.0	MT1	200	290	6	28,900
LMR200X115	11.5	MT1	200	290	6	30,600
LMR200X120	12.0	MT1	200	290	6	30,600
LMR200X125	12.5	MT1	200	290	6	32,100
LMR200X130	13.0	MT1	200	290	8	34,100
LMR200X135	13.5	MT1	200	290	8	34,100
LMR200X140	14.0	MT1	200	290	8	34,100
LMR200X145	14.5	MT2	200	330	8	36,700
LMR200X150	15.0	MT2	200	330	8	36,700
LMR200X155	15.5	MT2	200	330	8	37,700
LMR200X160	16.0	MT2	200	330	8	37,700
LMR200X165	16.5	MT2	200	330	8	39,500
LMR200X170	17.0	MT2	200	330	8	39,500
LMR200X175	17.5	MT2	200	330	8	40,400
LMR200X180	18.0	MT2	200	330	8	40,400
LMR200X185	18.5	MT2	200	330	8	42,400
LMR200X190	19.0	MT2	200	330	8	42,400
LMR200X195	19.5	MT2	200	330	8	44,300
LMR200X200	20.0	MT2	200	330	8	44,300
LMR200X205	20.5	MT2	200	330	8	46,500
LMR200X210	21.0	MT2	200	330	8	46,500
LMR200X215	21.5	MT2	200	330	8	49,400
LMR200X220	22.0	MT2	200	330	8	49,400
LMR200X225	22.5	MT2	200	330	8	58,800
LMR200X230	23.0	MT2	200	330	8	58,800
LMR200X235	23.5	MT3	200	349	8	60,200
LMR200X240	24.0	MT3	200	349	8	60,200
LMR200X245	24.5	MT3	200	349	8	65,700
LMR200X250	25.0	MT3	200	349	8	65,700
LMR200X260	26.0	MT3	200	349	10	73,500
LMR200X270	27.0	MT3	200	349	10	76,700
LMR200X280	28.0	MT3	200	349	10	80,300
LMR200X290	29.0	MT3	200	349	10	81,700
LMR200X300	30.0	MT3	200	349	10	85,300