


CoroMill® 360 insert for milling

KRINS 60°



		RE	BS	Ordering code	Dimensions, mm, inch														
					P		M		K		S		IC	LE	S				
					4220	4230	4240	2030	2040	3040	3220	3330				4220	2030	2040	
Heavy		19	1.6	2.2	360L-1906M-PH	☆										18.9	15.0	6.35	
			.063	.087													.746	.591	.250
			1.6	2.2	360R-19 06M-PH	☆	☆	☆					☆				18.9	15.0	6.35
			.063	.087													.746	.591	.250
		28	1.7	4.6	360L-2807M-PH		☆										28.5	20.0	7.94
			.067	.181													1.121	.787	.313
		1.7	4.6	360R-28 07M-PH	☆	☆	☆					☆				28.5	20.0	7.94	
		.067	.181													1.121	.787	.313	
		1.6	2.2	360L-1906M-MH				☆					☆			18.9	15.0	6.35	
		.063	.087													.746	.591	.250	
		1.6	2.2	360R-19 06M-MH			☆	☆					☆	☆		18.9	15.0	6.35	
		.063	.087													.746	.591	.250	
	28	1.7	4.6	360L-2807M-MH				☆					☆		28.5	20.0	7.94		
	.067	.181													1.121	.787	.313		
	1.7	4.6	360R-28 07M-MH			☆	☆					☆	☆		28.5	20.0	7.94		
	.067	.181													1.121	.787	.313		
	19	1.6	2.2	360L-1906M-KH						☆					18.9	15.0	6.35		
	.063	.087													.746	.591	.250		
	1.6	2.2	360R-19 06M-KH							☆	☆	☆			18.9	15.0	6.35		
	.063	.087													.746	.591	.250		
	28	1.7	4.6	360L-2807M-KH						☆					28.5	20.0	7.94		
	.067	.181													1.121	.787	.313		
	1.7	4.6	360R-28 07M-KH							☆	☆	☆			28.5	20.0	7.94		
	.067	.181													1.121	.787	.313		



J474



J508



Q1



Q17