


溶接式ネジスリーブ／溶接式ロングネジスリーブ／溶接式ライナ／溶接式ロングライナ／エキスバンド式ネジスリーブ
Male for Welding / Long Male for Welding / Liner for Welding / Long Liner for Welding / Male for Expanding

溶接式ネジスリーブ

Male for Welding

Type MAL-W





Nom.size	OD	ID	A	L	Mass kg
1.0 ^S	25.4	23	37.13-8ACME	21.5	0.07
1.25 ^S	31.8	29.4	43.16-8ACME	17	0.10
1.5 ^S	38.1	35.7	50.65-8ACME	21.5	0.12
2.0 ^S	50.8	47.8	64.16-8ACME	21.5	0.17
2.5 ^S	63.5	59.5	77.67-8ACME	21.5	0.22
3.0 ^S	76.3	72.3	91.19-8ACME	21.5	0.29
3.5 ^S	89.1	85.1	104.70-8ACME	21.5	0.36
4.0 ^S	101.6	97.6	119.25-6ACME	28	0.55

溶接式ロングネジスリーブ

Long Male for Welding

Type MAL2-W




Nom.size	OD	ID	A	L	Mass kg
1.0 ^S	25.4	23	37.13-8ACME	51	0.09
1.25 ^S	31.8	29.4	43.16-8ACME	51	0.12
1.5 ^S	38.1	35.7	50.65-8ACME	51	0.15
2.0 ^S	50.8	47.8	64.16-8ACME	51	0.22
2.5 ^S	63.5	59.5	77.67-8ACME	51	0.31
3.0 ^S	76.3	72.3	91.19-8ACME	51	0.40
3.5 ^S	89.1	85.1	104.70-8ACME	51	0.48
4.0 ^S	101.6	97.6	119.25-6ACME	56	0.69

溶接式ライナ

Liner for Welding

Type LNR-W





Nom.size	OD	ID	L	Mass kg
1.0 ^S	25.4	23	21.5	0.04
1.25 ^S	31.8	29.4	17	0.05
1.5 ^S	38.1	35.7	21.5	0.06
2.0 ^S	50.8	47.8	21.5	0.09
2.5 ^S	63.5	59.5	21.5	0.14
3.0 ^S	76.3	72.3	21.5	0.17
3.5 ^S	89.1	85.1	21.5	0.20
4.0 ^S	101.6	97.6	28	0.32

溶接式ロングライナ

Long Liner for Welding

Type LNR2-W




Nom.size	OD	ID	L	Mass kg
1.0 ^S	25.4	23	46	0.06
1.25 ^S	31.8	29.4	46	0.07
1.5 ^S	38.1	35.7	46	0.09
2.0 ^S	50.8	47.8	46	0.14
2.5 ^S	63.5	59.5	46	0.21
3.0 ^S	76.3	72.3	46	0.26
3.5 ^S	89.1	85.1	46	0.30
4.0 ^S	101.6	97.6	49	0.44

エキスバンド式ネジスリーブ

Male for Expanding

Type MAL-E



注：内側の溝は
ネジ用の溝ではありません。
The inside groove isn't the
groove for the screw.

Nom.size	OD	ID	A	L	Mass kg
1.0 ^S	29.5	25.7	37.13-8ACME	17	0.05
1.25 ^S	35.7	32.1	43.16-8ACME	16.5	0.07
1.5 ^S	42.5	38.4	50.65-8ACME	19.5	0.08
2.0 ^S	56	51.1	64.16-8ACME	19.5	0.12
* 2.5 ^S	69	63.8	77.67-8ACME	25	0.18
* 3.0 ^S	82	76.6	91.19-8ACME	30	0.25

*材質についてはお問い合わせ下さい
*2.5^S 及び 3.0^S は在庫が無くなりましたら販売を終了します。