



MTS Extra Length Drills

Codes


**242,
244 - 245**

Properties

M	WORKS STD.	HSS
TYPE N		
		BLUE FINISH
STANDARD POINT		

Suited Materials

GENERAL



d	l ₂ l ₁	200 315	300 400	300 450	375 500	375 530
No. 1 Morse Taper Shank						
10		2421000	-	-	-	-
10.5		2421050	-	-	-	-
11		2421100	2441100	-	-	-
11.5		2421150	-	-	-	-
12		2421200	2441200	-	-	-
13		2421300	2441300	-	-	-
14		2421400	2441400	-	-	-
No. 2 Morse Taper Shank						
15		2421500	2441500	-	-	-
16		2421600	2441600	-	2451600	-
17		2421700	2441700	-	2451700	-
18		2421800	2441800	-	2451800	-
19		2421900	2441900	-	2451900	-
20		2422000	2442000	-	2452000	-
21		2422100	2442100	-	2452100	-
22		2422200	2442200	-	2452200	-
23		2422300	2442300	-	2452300	-
No. 3 Morse Taper Shank						
24		-	-	2442400	2452400	-
25		-	-	2442500	2452500	-
26		-	-	2442600	2452600	-
27		-	-	2442700	2452700	-
28		-	-	2442800	2452800	-
29		-	-	2442900	2452900	-
30		-	-	2443000	2453000	-
No. 4 Morse Taper Shank						
32		-	-	2443200	-	2453200
35		-	-	2443500	-	2453500
38		-	-	2443800	-	2453800
40		-	-	2444000	-	2454000
42		-	-	2444200	-	2454200
45		-	-	2444500	-	2454500
48		-	-	2444800	-	2454800
50		-	-	2445000	-	2455000



**MORSE TAPER
SHANK DRILLS**