







Auto Roughing insert for milling



		 RE BS	Ordering code	Dimensions, mm, inch															
				P		M	K				H		IC	LE	S				
Light		12 2.0 1.8 .079 .069	TNEF 12 04 AN-WL	☆													12.7 12.0 4.76 .500 .472 .187		
		12 2.0 1.3 .079 .049	TNEF 12 04 AN-KM								☆			☆	☆			12.7 12.0 4.76 .500 .472 .187	
Medium		12 1.0 1.3 .039 .049	TNEF 12 04 AN-KX													☆	12.7 12.0 4.76 .500 .472 .187		
		12 3.0 1.5 .118 .059	TNEF 12 04 AN-CA	☆							☆	☆				☆	☆	12.7 12.0 4.76 .500 .472 .187	
		12 2.5 .098	TNEN 12 04 AN	☆								☆	☆				☆	☆	12.7 12.0 4.76 .500 .472 .187
		12 3.0 1.5 .118 .059	TNHF 12 04 AN-CA		☆	☆	☆	☆					☆	☆					12.7 12.0 4.76 .500 .472 .187

Advanced cutting materials

		 BS	Ordering code	Dimensions, mm, inch													
				K		H	IC	LE	S								
Light		12 2.5 .098	TNCN 12 04 ANE	☆	☆												12.7 12.0 4.76 .500 .472 .187
		12 2.5 .098	TNCN 12 04 AN	☆	☆												

