





# CoroMill® 690 insert for milling



## End insert

		RE	BS	Ordering code	s			Dimensions, mm, inch						
					1030	2040	S30T	S40T	W1	LE	S			
M		10E	0.8	1.0	690-100508M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.031	.039						.394	.394	.205		
			1.2	1.0	690-100512M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.047	.039						.394	.394	.205		
			1.6	1.0	690-100516M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.063	.039						.394	.394	.205		
			2.0	1.0	690-100520M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.079	.039						.394	.394	.205		
			2.4	1.0	690-100524M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.094	.039						.394	.394	.205		
			3.1	1.0	690-100531M-E-SL	☆	☆	☆	☆	10.0	10.0	5.20		
			.122	.039						.394	.394	.205		
		N	Light	14E	0.8	1.0	690-140608M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35
					.031	.039						.571	.581	.250
					1.2	1.0	690-140612M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35
					.047	.039						.571	.581	.250
	1.6			1.0	690-140616M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35		
	.063			.039						.571	.581	.250		
	2.0			1.0	690-140620M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35		
	.079			.039						.571	.581	.250		
	2.4			1.0	690-140624M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35		
	.094			.039						.571	.581	.250		
O	Light	3.1	1.0	690-140631M-E-SL	☆	☆	☆	☆	14.5	14.7	6.35			
			.122	.039						.571	.581	.250		
		4.0	1.0	690-140640M-E-SL	☆	☆	☆	☆	14.5	15.2	6.35			
			.157	.039						.571	.600	.250		
		5.0	1.0	690-140650M-E-SL	☆	☆	☆	☆	14.5	15.7	6.35			
			.197	.039						.571	.620	.250		
		6.0	1.0	690-140660M-E-SL	☆	☆	☆	☆	14.5	16.5	6.35			
			.236	.039						.571	.650	.250		
	6.4	1.0	690-140664M-E-SL	☆	☆	☆	☆	14.5	16.7	6.35				
	.250	.039						.571	.659	.250				

## Peripheral insert

		RE	Ordering code	s				Dimensions, mm, inch			
				1030	2040	S30T	S40T	IC	LE	S	
P	Light	10P	1.0	690-100510M-P-SL	☆	☆	☆	☆	10.0	9.0	5.20
			.039						.394	.354	.205
		14P	1.0	690-140610M-P-SL	☆	☆	☆	☆	14.5	13.5	6.35
			.039						.571	.531	.250




J474



J508



Q1



Q17