



# CoroMill® Plura solid carbide square shoulder end mill

Straight corner radius, center cut


End mills for heavy duty milling

CNSC 1  
 FHA 38°  
 BSG COROMANT  
 TCDC h10  
 TCDCON h6



## Metric version

DC	CZC <sub>MS</sub>	APMX	RE	LU	ZEFP	Ordering code	M S		Dimensions		
							1740	1740	DCON	LF	
6.0	6	13.0	0.50	13.0	4	2S342-0600-050CMA	☆	☆	6.0	57.0	20
	6	13.0	1.00	13.0	4	2S342-0600-100CMA	☆	☆	6.0	57.0	20
8.0	8	18.0	0.50	18.0	4	2S342-0800-050CMA	☆	☆	8.0	63.0	20
	8	18.0	1.00	18.0	4	2S342-0800-100CMA	☆	☆	8.0	63.0	20
	8	18.0	1.50	18.0	4	2S342-0800-150CMA	☆	☆	8.0	63.0	20
	8	18.0	2.00	18.0	4	2S342-0800-200CMA	☆	☆	8.0	63.0	20
10.0	10	22.0	0.50	22.0	4	2S342-1000-050CMA	☆	☆	10.0	72.0	20
	10	22.0	1.00	22.0	4	2S342-1000-100CMA	☆	☆	10.0	72.0	20
	10	22.0	1.50	22.0	4	2S342-1000-150CMA	☆	☆	10.0	72.0	20
	10	22.0	2.00	22.0	4	2S342-1000-200CMA	☆	☆	10.0	72.0	20
	10	22.0	3.00	22.0	4	2S342-1000-300CMA	☆	☆	10.0	72.0	20
12.0	12	26.0	0.50	26.0	4	2S342-1200-050CMA	☆	☆	12.0	83.0	20
	12	26.0	1.00	26.0	4	2S342-1200-100CMA	☆	☆	12.0	83.0	20
	12	26.0	1.50	26.0	4	2S342-1200-150CMA	☆	☆	12.0	83.0	20
	12	26.0	2.00	26.0	4	2S342-1200-200CMA	☆	☆	12.0	83.0	20
	12	26.0	3.00	26.0	4	2S342-1200-300CMA	☆	☆	12.0	83.0	20
16.0	16	34.0	0.50	34.0	4	2S342-1600-050CMA	☆	☆	16.0	92.0	20
	16	34.0	1.00	34.0	4	2S342-1600-100CMA	☆	☆	16.0	92.0	20
	16	34.0	2.00	34.0	4	2S342-1600-200CMA	☆	☆	16.0	92.0	20
	16	34.0	3.00	34.0	4	2S342-1600-300CMA	☆	☆	16.0	92.0	20
	16	34.0	4.00	34.0	4	2S342-1600-400CMA	☆	☆	16.0	92.0	20
	16	34.0	5.00	34.0	4	2S342-1600-500CMA	☆	☆	16.0	92.0	20
20.0	20	42.0	1.00	42.0	4	2S342-2000-100CMA	☆	☆	20.0	104.0	20
	20	42.0	2.00	42.0	4	2S342-2000-200CMA	☆	☆	20.0	104.0	20
	20	42.0	3.00	42.0	4	2S342-2000-300CMA	☆	☆	20.0	104.0	20
	20	42.0	4.00	42.0	4	2S342-2000-400CMA	☆	☆	20.0	104.0	20
	20	42.0	5.00	42.0	4	2S342-2000-500CMA	☆	☆	20.0	104.0	20
	20	42.0	6.35	42.0	4	2S342-2000-635CMA	☆	☆	20.0	104.0	20



L15

