


# T-Max® P insert for turning

Rhombic 80°



		ISO CODE	P								M					K				S				ANSI CODE							
			1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	H13A		H13A	1105	1115	1125	GC15	H13A	S05F
D		12 1/2	CNMG 12 04 04-PMC					☆	☆																					CNMG 431-PMC	
			CNMG 12 04 08-PMC					☆	☆																					CNMG 432-PMC	
			CNMG 12 04 12-PMC					☆	☆																						CNMG 433-PMC
		16 5/8	CNMG 16 06 08-PMC					☆	☆																					CNMG 542-PMC	
			CNMG 16 06 12-PMC					☆	☆																						CNMG 543-PMC
			CNMG 16 06 16-PMC					☆	☆																						CNMG 544-PMC
E		12 1/2	CNMG 12 04 04-SMC																					☆					CNMG 431-SMC		
			CNMG 12 04 08-SMC																					☆					CNMG 432-SMC		
			CNMG 12 04 12-SMC																					☆						CNMG 433-SMC	
		16 5/8	CNMG 16 06 08-SMC																					☆						CNMG 542-SMC	
			CNMG 16 06 12-SMC																					☆						CNMG 543-SMC	
			CNMG 16 06 16-SMC																					☆						CNMG 544-SMC	
F		12 1/2	CNMG 12 04 08-WM		☆	☆	☆					☆				☆		☆	☆										CNMG 432-WM		
			CNMG 12 04 12-WM		☆	☆	☆					☆				☆		☆	☆										CNMG 433-WM		
		16 5/8	CNMG 16 06 08-WM				☆																						CNMG 542-WM		
			CNMG 16 06 12-WM				☆																							CNMG 543-WM	
		12 1/2	CNMG 12 04 08-WMX			☆	☆	☆					☆				☆		☆	☆										CNMG 432-WMX	
			CNMG 12 04 12-WMX			☆	☆	☆					☆				☆		☆	☆										CNMG 433-WMX	
G		16 5/8	CNMG 16 06 08-WMX			☆	☆	☆				☆				☆		☆	☆										CNMG 542-WMX		
			CNMG 16 06 12-WMX			☆	☆	☆				☆				☆		☆	☆										CNMG 543-WMX		
		09 3/8	CNMG 09 03 04-PM					☆	☆	☆																				CNMG 321-PM	
			CNMG 09 03 08-PM					☆	☆	☆																				CNMG 322-PM	
		12 1/2	CNMG 12 04 04-PM					☆	☆	☆																				CNMG 431-PM	
			CNMG 12 04 08-PM					☆	☆	☆																				CNMG 432-PM	
H			CNMG 12 04 12-PM					☆	☆	☆																			CNMG 433-PM		
			CNMG 12 04 16-PM					☆	☆	☆																			CNMG 434-PM		
		16 5/8	CNMG 16 06 08-PM					☆	☆	☆																			CNMG 542-PM		
			CNMG 16 06 12-PM					☆	☆	☆																				CNMG 543-PM	
			CNMG 16 06 16-PM					☆	☆	☆																				CNMG 544-PM	
		19 3/4	CNMG 19 06 08-PM					☆	☆	☆																				CNMG 642-PM	
			CNMG 19 06 12-PM					☆	☆	☆																				CNMG 643-PM	
			CNMG 19 06 16-PM					☆	☆	☆																				CNMG 644-PM	

For dimensions, see code key on page I14.

