



# 83000 | ROCKET 3 hammer drill bit SDS-plus shank

Art.-Group 41



The next generation hammer drill bit designed and manufactured with state-of-the-art technology for maximum drilling speed and unprecedented stability

- ▶ Made of high-quality tempering steel specially selected for the toughest applications
- ▶ 3 crushers achieve with impact and torsion maximum drilling speed and ultimate destruction
- ▶ Core-reinforced spiral ensures highest breaking stability even under extreme stress
- ▶ 2-flute geometry with large-volume spiral
- ▶ Accurate drilling without slipping off the material
- ▶ The PGM-Certification guarantees accurate dowel holes and precise concentricity
- ▶ Wear marks show, whether the tool is still suitable to drill dowel-compatible holes
- ▶ For drill bits longer than 450 mm, it is recommended to pre-drill with a shorter drill of the same diameter

Single packaging with hanger

Ø mm	L1 mm	L2 mm	Art.-No.
3.0	110	50	8 303 110
4.0	110	50	8 304 110
4.0	160	100	8 304 160
5.0	110	50	8 305 110
5.0	160	100	8 305 160
5.0	210	150	8 305 210
5.0	260	200	8 305 260
5.0	310	250	8 305 310
5.0	360	300	8 305 360
5.0	450	390	8 305 450
5.5	110	50	83 055 110
5.5	160	100	83 055 160
5.5	210	150	83 055 210
5.5	260	200	83 055 260
5.5	310	250	83 055 310
5.5	410	350	83 055 410
6.0	110	50	8 306 110
6.0	160	100	8 306 160
6.0	210	150	8 306 210
6.0	260	200	8 306 260
6.0	310	250	8 306 310
6.0	460	400	8 306 450
6.5	110	50	83 065 110
6.5	160	100	83 065 160
6.5	210	150	83 065 210
6.5	260	200	83 065 260
6.5	310	250	83 065 310
6.5	450	390	83 065 450
7.0	110	50	8 307 110
7.0	160	100	8 307 160
7.0	210	150	8 307 210
7.0	250	190	8 307 250

Ø mm	L1 mm	L2 mm	Art.-No.
8.0	110	50	8 308 110
8.0	160	100	8 308 160
8.0	210	150	8 308 210
8.0	260	200	8 308 260
8.0	310	250	8 308 310
8.0	400	340	8 308 400
8.0	460	400	8 308 460
8.0	600	540	8 308 600
8.0	1000	940	83 081 000
9.0	160	100	8 309 160
9.0	210	150	8 309 210
10.0	110	50	8 310 110
10.0	160	100	8 310 160
10.0	210	150	8 310 210
10.0	260	200	8 310 260
10.0	310	250	8 310 310
10.0	350	290	8 310 350
10.0	450	390	8 310 450
10.0	600	540	8 310 600
10.0	800	740	8 310 800
10.0	1000	940	83 101 000
11.0	160	100	8 311 160
11.0	260	200	8 311 260
12.0	160	110	8 312 166
12.0	210	160	8 312 216
12.0	260	210	8 312 266
12.0	310	260	8 312 310
12.0	360	310	8 312 360
12.0	450	400	8 312 450
12.0	600	550	8 312 600
12.0	1000	950	83 121 000
13.0	160	110	8 313 166
13.0	260	210	8 313 266
13.0	310	260	8 313 310

Ø mm	L1 mm	L2 mm	Art.-No.
13.0	450	400	8 313 450
14.0	160	110	8 314 166
14.0	210	160	8 314 216
14.0	260	210	8 314 266
14.0	310	260	8 314 310
14.0	450	400	8 314 450
14.0	600	550	8 314 600
14.0	1000	950	83 141 000
15.0	160	110	8 315 166
15.0	210	160	8 315 210
15.0	260	210	8 315 266
16.0	160	110	8 316 166
16.0	210	160	8 316 216
16.0	260	210	8 316 260
16.0	310	260	8 316 300
16.0	450	400	8 316 450
16.0	600	550	8 316 600
16.0	800	750	8 316 800
16.0	1000	950	83 161 000
17.0	210	160	8 317 200
17.0	310	260	8 317 310
18.0	200	150	8 318 200
18.0	300	250	8 318 300
18.0	450	400	8 318 450
18.0	600	550	8 318 600
18.0	1000	950	83 181 000
19.0	200	150	8 319 200
19.0	450	400	8 319 450
20.0	200	150	8 320 200
20.0	300	250	8 320 300
20.0	450	400	8 320 450
20.0	600	550	8 320 600
20.0	1000	950	83 201 000

Note: Special dimensions on request. Also possible in lengths over 1,000 mm.