

För icke direkt toleranssatta mått gäller toleransklass
 General tolerances if not otherwise stated



NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
 No sharp edges unless otherwise specified.


Övriga generella toleranser enligt ritning 4100-4644.
 Additional general tolerances in accordance with drawing 4100-4644.

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
9	1043210000	1029587001 W 1029587000	090710	SE
10	1052406000	4101-2330 Ändrad/Changed	110404	SE



PACKAS I 10-PACKLÅDA 4101-2551
 PACKED IN 10 PCS BOX 4101-2551

SKALA/SCALE 1:2



4101-4487 TILLTRYCK PÅ KORT ENLIGT OMT DOKUMENT NR.:1029587001
 PRINTING ON CARD ACCORDING TO OMT DOCUMENT NO.:1029587001

Material		Behandling/Treatment			Status	
Konstr./Design JOWI		Ritad/Drawn TGW	Datum/Date 2011-04-04	Skala/Scale 1:1	Kontr./Checked SE	Godk./Approved NE
pressmaster® Embla + raktblad kassett Embla + straight blade cassette				Vikt/Weight, gram 168g		Art grp 012
ISO 9001 REG NR FM13647				Ritn nr./Drawing no 43200612		REV 010

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
 This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.