

# SANDERS


Self Vacuum Orbital Sander • Orbital Sanders • Disc Sanders

## SI-3007


SI-3007M : Velcro pad model

Orbital Sander


- Paper size : 100mm x 180mm
- The tool has paper clips and you can use roll paper abrasive of 100mm width
- One hand grip for easy operation



ORBITAL




Standard Accessory



SI-3007M

Standard Accessory



SI-3007

Paper clip



Pad/Disc Size mm/(in.)	95x175
Orbit Dia mm	5
Free Speed r.p.m.	11,000
Out Put Watt	275
Weight kg/(lb)	1.82/(4.00)
Noise Level dBA/(power)	86/(97)
Vibration a/k m/s <sup>2</sup>	27.5/3.2
Max Air Consumption CFM/(L/S)	16.8/(7.9)
Avg Air Consumption CFM/(L/S)	2.8/(1.3)

IMPACT  
WRENCHES

DRIVERS

BATCHET  
WRENCHES

SANDERS

POLISHERS

GRINDERS

DRILLS  
SPOTMILLS

CUTTING TOOLS

OTHERS

INDUSTRIAL  
TOOLS

ACCESSORIES

SOUND,  
VIBRATION

MAINTENANCE  
CHECK

QUALITY


## SI-3018A

Self Vacuum Orbital Sander


## SI-3018AM

Self Vacuum Orbital Sander with velcro pad


- Self vacuum orbital sander with bar grip
- Paper size : 100mm x 180mm
- With leather pad or Velcro pad



ORBITAL



Standard Accessory



SI-3018AM

Standard Accessory



SI-3018A



Pad/Disc Size mm/(in.)	95x175
Orbit Dia mm	5
Free Speed r.p.m.	7,000
Out Put Watt	222
Weight kg/(lb)	2.31/(5.09)
Noise Level dBA/(power)	83/(94)
Vibration a/k m/s <sup>2</sup>	10.2/1.5
Max Air Consumption CFM/(L/S)	18.6/(8.8)
Avg Air Consumption CFM/(L/S)	3.1/(1.5)

## SI-3003B


Orbital Sander

## SI-3003BM


Orbital Sander with velcro pad

Heavy Duty Type


- Light weight & heavyduty orbital sander
- Paper size : 75mm x 110mm



ORBITAL



Standard Accessory



SI-3003BM

Standard Accessory



SI-3003B



Pad/Disc Size mm/(in.)	75x100
Orbit Dia mm	4
Free Speed r.p.m.	8,000
Out Put Watt	134
Weight kg/(lb)	1.05/(2.31)
Noise Level dBA/(power)	88/(99)
Vibration a/k m/s <sup>2</sup>	4.6/0.9
Max Air Consumption CFM/(L/S)	16.8/(7.9)
Avg Air Consumption CFM/(L/S)	2.8/(1.3)

## SI-2026

Disc Sander



SINGLE ACTION



Standard Accessory




136-45

Pad/Disc Size mm/(in.)	125/(5")
Spindle Size	5/8-11UNC
Free Speed r.p.m.	5,500
Out Put Watt	491
Weight kg/(lb)	1.50/(3.31)
Noise Level dBA/(power)	88/(99)
Vibration a/k m/s <sup>2</sup>	3.4/0.8
Max Air Consumption CFM/(L/S)	26.4/(12.5)
Avg Air Consumption CFM/(L/S)	4.4/(2.1)

## SI-2351

Disc Sander



SINGLE ACTION



Standard Accessory



820-52

Pad/Disc Size mm/(in.)	180/(7")
Spindle Size	5/8-11UNC
Free Speed r.p.m.	4,500
Out Put Watt	458
Weight kg/(lb)	2.13/(4.70)
Noise Level dBA/(power)	80/(91)
Vibration a/k m/s <sup>2</sup>	4.9/0.9
Max Air Consumption CFM/(L/S)	24.6/(11.6)
Avg Air Consumption CFM/(L/S)	4.1/(1.9)