


PC

Male Straight
ØD



MODEL [ØD-T] Tube(Inch)-Thread(NPT)

(mm)


MODEL	ØD	R	A	B	C	H1	H2	X	Y	Orifice (Ømm)	W.G(g)	Q'ty/Inbox
PC 5/32-U10U	5/32	UNF10 * 32	4	22	16	7/16	2.4	10	12	2	8.4	100
PC 5/32-N01U	5/32	NPT1/8	8	22	16	7/16	2.4	10	12	3	9.4	100
PC 5/32-N02U	5/32	NPT1/4	11	22	16	9/16	2.4	10	12	3	15.5	100
PC 5/32-N03U	5/32	NPT3/8	12	22	16	11/16	2.4	10	12	3	26.1	50
PC 3/16-U10U	3/16	UNF10 * 32	4	23.8	17	7/16	2.4	11	13	2	9	100
PC 3/16-N01U	3/16	NPT1/8	8	23.3	17	7/16	4	11	13	4	9.3	100
PC 3/16-N02U	3/16	NPT1/4	11	23.3	17	9/16	4	11	13	4	16.5	100
PC 3/16-N03U	3/16	NPT3/8	12	23.3	17	11/16	4	11	13	4	27.3	50
PC 1/4-U10U	1/4	UNF10 * 32	4	25	17	1/2	2.4	12	14	2	11.8	100
PC 1/4-N01U	1/4	NPT1/8	8	23.5	17	1/2	4	12	14	4	10.3	100
PC 1/4-N02U	1/4	NPT1/4	11	25.5	17	9/16	4	12	14	4	17.5	100
PC 1/4-N03U	1/4	NPT3/8	12	25	17	11/16	4	12	14	4	24.1	50
PC 1/4-N04U	1/4	NPT1/2	15	25	17	11/16	4	12	14	4	47.8	50
PC 5/16-N01U	5/16	NPT1/8	8	28.9	18.5	9/16	4.8	14	16	4	16.4	100
PC 5/16-N02U	5/16	NPT1/4	11	27.4	18.5	9/16	5.6	14	16	6	18.1	100
PC 5/16-N03U	5/16	NPT3/8	12	25.7	18.5	11/16	5.6	14	16	6	25.8	50
PC 5/16-N04U	5/16	NPT1/2	15	28.7	18.5	7/8	5.6	14	16	6	49.6	50
PC 3/8-N01U	3/8	NPT1/8	8	31.5	21	11/16	4.8	17	19	4	25.6	50
PC 3/8-N02U	3/8	NPT1/4	11	34.5	21	11/16	5.6	17	19	6	29.6	50
PC 3/8-N03U	3/8	NPT3/8	12	30.5	21	11/16	8	17	19	8	27.7	50
PC 3/8-N04U	3/8	NPT1/2	15	30	21	7/8	8	17	19	8	48.8	50
PC 1/2-N01U	1/2	NPT1/8	8	33.9	22.5	7/8	4	21	23	4	37.9	50
PC 1/2-N02U	1/2	NPT1/4	11	27.4	22.5	7/8	6.4	21	23	6	41.7	50
PC 1/2-N03U	1/2	NPT3/8	12	32.5	22.5	7/8	7.9	21	23	8	39	50
PC 1/2-N04U	1/2	NPT1/2	15	34.5	22.5	7/8	7.9	21	23	8	50.6	25

MODEL [ØD-T] Tube(Inch)-Thread(NPT)

(mm)

PL

Male Elbow
ØD



MODEL	ØD	R	ØP	A	B	C	E	H	X	Y	Orifice (Ømm)	W.G(g)	Q'ty/Inbox
PL 5/32-U10U	5/32	UNF10 * 32	10.4	5.5	22.1	16	18.1	7/16	10	12	2	9.5	100
PL 5/32-N01U	5/32	NPT1/8	10.4	8	24.6	16	18.1	7/16	10	12	2.6	11.7	100
PL 5/32-N02U	5/32	NPT1/4	10.4	11	27.6	16	18.1	9/16	10	12	2.6	18	100
PL 5/32-N03U	5/32	NPT3/8	10.4	12	28.6	16	18.1	11/16	10	12	2.6	25	50
PL 3/16-U10U	3/16	UNF10 * 32	11	5.5	22.5	17	19.1	7/16	11	13	2	10	100
PL 3/16-N01U	3/16	NPT1/8	11	8	25	17	19.1	7/16	11	13	2.6	11.9	100
PL 3/16-N02U	3/16	NPT1/4	11	11	28	17	19.1	9/16	11	13	2.6	17.9	100
PL 3/16-N03U	3/16	NPT3/8	11	12	29	17	19.1	11/16	11	13	2.6	26.8	50
PL 1/4-U10U	1/4	UNF10 * 32	12.4	5.5	23.1	17	20.6	1/2	12	14	2	11.2	100
PL 1/4-N01U	1/4	NPT1/8	12.4	8	25.1	17	20.6	1/2	12	14	4.6	13.6	100
PL 1/4-N02U	1/4	NPT1/4	12.4	11	29.1	17	20.6	9/16	12	14	4.6	21.5	50
PL 1/4-N03U	1/4	NPT3/8	12.4	12	31.1	17	20.6	11/16	12	14	4.6	32.9	50
PL 1/4-N04U	1/4	NPT1/2	12.4	15	35	17	20.6	7/8	12	14	4.6	45	50
PL 5/16-N01U	5/16	NPT1/8	14.4	8	27	18.5	22.7	9/16	14	16	5	16.3	50
PL 5/16-N02U	5/16	NPT1/4	14.4	11	31	18.5	22.7	9/16	14	16	6	23.4	50
PL 5/16-N03U	5/16	NPT3/8	14.4	12	32	18.5	22.7	11/16	14	16	6	31.4	50
PL 5/16-N04U	5/16	NPT1/2	14.4	15	36	18.5	22.7	7/8	14	16	6	52	25
PL 3/8-N01U	3/8	NPT1/8	17.6	8	32	21	26.1	11/16	17	19	5	29.7	50
PL 3/8-N02U	3/8	NPT1/4	17.6	11	35	21	26.1	11/16	17	19	8	32.4	25
PL 3/8-N03U	3/8	NPT3/8	17.6	12	36	21	26.1	11/16	17	19	8	40.9	25
PL 3/8-N04U	3/8	NPT1/2	17.6	15	39	21	26.1	7/8	17	19	8	55.6	25
PL 1/2-N01U	1/2	NPT1/8	21.2	8	34	22.5	29.3	7/8	21	23	5	40.8	25
PL 1/2-N02U	1/2	NPT1/4	21.2	11	37	22.5	29.3	7/8	21	23	7	44.5	25
PL 1/2-N03U	1/2	NPT3/8	21.2	12	38	22.5	29.3	7/8	21	23	9	48.4	25
PL 1/2-N04U	1/2	NPT1/2	21.2	15	41	22.5	29.3	7/8	21	23	9	60.3	25