


JEP-0.6, 1.2, 2.5, 5 Through Shaft Type

Model	Clutch model used	Brake model used	Static friction torque (Nm)	Rated voltage (DC-V)	Power consumption at 75°C(W)		Mass(kg)
					Clutch	Brake	
JEP-0.6	JCC-0.6F	JB-0.6	6	24	8	8	2.6
JEP-1.2	JCC-1.2F	JB-1.2	12	24	11	11	4.5
JEP-2.5	JCC-2.5F	JB-2.5	25	24	16	14	8.4
JEP-5	JCC-5F	JB-5	50	24	23	20	14



(DIM: mm)

Model	Diameter direction								Shaft direction		
	A	B	C	D	E	F	G	H	L	M	N
JEP-0.6	105	40	63	105	30	69	9	115.5	198	130	55
JEP-1.2	128	45	71	128	35	79	11	135	236	150	65
JEP-2.5	154	60	90	154	40	89	13	167	295	190	80
JEP-5	188	75	100	188	50	106	15	194	360	220	90

Model	Shaft direction				Shaft hole					
	O	P	R	Z	Q	QK	d	b	h	t
JEP-0.6	30	99	72.5	7	25	18	12	4	4	2.5
JEP-1.2	40	118	86.5	7	30	25	15	5	5	3
JEP-2.5	50	147.5	106	10	40	34	20	6	6	3.5
JEP-5	60	180	128	12	50	38	25	8	7	4