


CoroMill® 490 insert for milling

KRINS 90°



	RE	BS	Ordering code	P												M					K					N		S			H		Dimensions, mm, inch															
				1010	1030	3040	3040	3220	4220	4230	4240	530	1030	1040	2030	2040	4240	530	S30T	1010	1020	3040	3220	3330	4220	4230	4240	H13A	H13A	1010	1030	2040	S30T	S40T	1010	1030	530	IC	LE	S								
Light	08	0.4	1.5	490R-08T304M-PL	☆	☆																																8.5	5.6	3.30								
																																									.335	.220	.130					
			0.8	1.2	490R-08T308M-PL	☆	☆																																		8.5	5.6	3.30					
																																										.335	.220	.130				
			14	0.8	2.0	490R-140408M-PL	☆	☆																																			13.8	10.3	3.90			
																																												.543	.406	.154		
	Light	08	0.4	1.5	490R-08T304E-ML																																					8.5	5.6	3.30				
																																												.335	.220	.130		
				0.8	1.2	490R-08T308E-ML	☆	☆																																				8.5	5.6	3.30		
																																													.335	.220	.130	
				14	0.8	2.0	490R-140408E-ML																																						13.8	10.3	3.90	
																																														.543	.406	.154
Medium	08	0.4	1.5	490R-08T304M-KL																																						8.5	5.6	3.30				
																																												.335	.220	.130		
			0.8	1.2	490R-08T308M-KL																																							8.5	5.6	3.30		
																																													.335	.220	.130	
		Medium	08	0.8	1.2	490R-08T308M-PM	☆	☆																																					8.5	5.6	3.30	
																																																.335
	1.2			0.9	490R-08T312M-PM	☆	☆																																						8.5	5.6	3.30	
																																														.335	.220	.130
	1.6			0.6	490R-08T316M-PM	☆	☆																																						8.5	5.6	3.30	
																																														.335	.220	.130
Medium	14	0.8	2.0	490R/L-140408M-PM																																								13.8	10.3	3.90		
																																														.543	.406	.154
			0.8	2.0	490R-140408M-PM	☆																																							13.8	10.3	3.90	
																																														.543	.406	.154
			1.2	2.0	490R-140412M-PM	☆	☆																																							13.8	10.3	3.90
																																															.543	.406
Medium	1.6	1.2	490R-140416M-PM	☆	☆																																								13.8	10.3	3.90	
																																														.543	.406	.154
Medium	2.0	0.9	490R-140420M-PM	☆	☆																																								13.8	10.3	3.90	
																																														.543	.406	.154



J474



J508



Q1



Q17

