



# ドリルチャックアーバ

## JACOBS TAPER ARBOR

①-D<sub>1</sub>-J(No.)



MODEL	CODE	øD <sub>1</sub>	JT No.	øD <sub>2</sub>	L	H <sub>1</sub>	H <sub>2</sub>	N/W (kg)
20-J6	35528	20	6	17. 170	60	24	4	0. 19
25-J6	35536	25	6	17. 170	80	24	4	0. 35
32-J6	35558	32	6	17. 170	80	24	4	0. 55
-J3	35560		3	20. 599				0. 59
42-J6	35590	42	6	17. 170	80	24	4	0. 91

注: 1. ドリルチャックは付属していません。別途お求め下さい。  
NOTE: 1. Drill chuck is sold separately.

### ご注文例 ORDERING EXAMPLE



① 20 - ② J ③ 6

① シャンクサイズ øD<sub>1</sub> Shank Size øD<sub>1</sub>  
② 呼称 Name  
③ JT No. JT No.

# モールステーパコレット

## MORSE TAPER COLLET

①-D-MT(No.)



MODEL	CODE	FIG.	øD	øC	L	L <sub>1</sub>	MT		N/W (kg)	
							MT No.	ød		
20-MT1	35522	1	20	23. 5	56	20	1	12. 065	0. 16	
-MT2	35524				58	35	2	17. 780	0. 13	
25-MT1	35532		25	31	66	15	1	12. 065	0. 27	
-MT2	35534				73	20	2	17. 780	0. 24	
32-MT1	35552		2	32	37. 5	66	15	1	12. 065	0. 47
-MT2	35554					71	20	2	17. 780	0. 46
-MT3	35556	3				23. 825	0. 35			
42-MT1	35582	1	42	47. 5	76	20	1	12. 065	1. 02	
-MT2	35584				77	15	2	17. 780	0. 93	
-MT3	35586				3	23. 825	0. 76			
-MT4	35588				2	31. 267	0. 75			

### ご注文例 ORDERING EXAMPLE

① 20 - ② MT ③ 1

① シャンクサイズ øD Shank Size øD  
② 呼称 Name  
③ MT No. MT No.