


CoroMill® Plura solid carbide square shoulder end mill

Straight, center cut

End mills with chip-breaker profile

R216.3x..40-AC..U

CNSC 0
 FHA 40°
 BSG DIN 6527 L
 TCDCON h6




Metric version

DC	CZC _{MS}	APMX	CHW	KCH	LU	ZEFP	Ordering code	HTC	Dimensions
									DCON RMPX LF
6.00	6.0	13.00	0.45	35°	13.00	3	R216.33-06040-AC13U	☆	6.00 15° 57.00
8.00	8.0	19.00	0.45	35°	19.00	3	R216.33-08040-AC19U	☆	8.00 15° 63.00
10.00	10.0	22.00	0.58	35°	22.00	3	R216.33-10040-AC22U	☆	10.00 15° 72.00
12.00	12.0	26.00	0.58	35°	26.00	3	R216.33-12040-AC26U	☆	12.00 15° 83.00
14.00	14.0	26.00	0.70	35°	26.00	3	R216.33-14040-AC26U	☆	14.00 15° 83.00
16.00	16.0	32.00	0.70	35°	32.00	3	R216.33-16040-AC32U	☆	16.00 15° 92.00
18.00	18.0	32.00	0.70	35°	32.00	3	R216.33-18040-AC32U	☆	18.00 15° 92.00
20.00	20.0	38.00	0.70	35°	38.00	3	R216.33-20040-AC38U	☆	20.00 15° 104.00



O5



J490



J508



Q1



Q35



Q24