

## TORQUE WRENCH, SINGLE PURPOSE TYPE

Calibration Certificate Included

Test Report

Traceability Chart


Single purpose type torque wrench which is set in requested torque value when ordered. When preset torque has been reached, a click sound will occur with slight force from the wrench.



Models	Torque Range (N·m)	Units	Sq.dr A (mm)	Dimensions (mm)				Hand force at Max. torque (N)	Suitable bolt		Qty./ Carton	Weight (kg)	Case Dimensions
				B	H	T	L		Ordinary	High strength			
T2MP6	1 ~ 6	N·m	6.35	24.0	18.3	10.4	211	40	M4 ~ M6	M4	1	0.19	305 × 97 × 70
T2MP13	3 ~ 13	N·m	6.35	24.0	18.3	10.4	240	72	M6 ~ M8	M5 ~ M6	1	0.24	305 × 97 × 70
T3MP20	4 ~ 20	N·m	9.5	24.0	21.6	10.4	240	111	M6 ~ M8	M5 ~ M6	1	0.25	305 × 97 × 70
T3MP50	10 ~ 50	N·m	9.5	36.0	26.4	14.0	291	227	M10	M8	1	0.49	355 × 97 × 70
T4MP50	10 ~ 50	N·m	12.7	36.0	30.4	14.0	291	227	M10	M8	1	0.50	355 × 97 × 70
T3MP100	20 ~ 100	N·m	9.5	36.0	26.4	14.0	369	336	M12 ~ M14	M10	1	0.67	505 × 97 × 70
T4MP100	20 ~ 100	N·m	12.7	36.0	30.4	14.0	369	336	M12 ~ M14	M10	1	0.68	505 × 97 × 70
T4MP140	30 ~ 140	N·m	12.7	36.0	30.4	14.0	432	388	M14	M10 ~ M12	1	0.80	505 × 97 × 70
T4MP200	40 ~ 200	N·m	12.7	45.2	34.0	17.8	505	554	M14 ~ M16	M12	1	1.39	765 × 97 × 70
T4MP300	40 ~ 300	N·m	12.7	45.2	34.0	17.8	696	491	M14 ~ M20	M12 ~ M14	1	1.82	765 × 97 × 70
T6MP300	40 ~ 300	N·m	19.0	45.2	40.5	17.8	696	491	M14 ~ M20	M12 ~ M14	1	1.86	765 × 97 × 70

- N·m specification
- Torque Accuracy ± 3%
- ※ Use hex key (A/F 3 mm) to set torque for T2MP6 - T3MP20.
- ※ Use hex key (A/F 5 mm) to set torque for T3MP50 - T6MP300.

Accessory	
Tool for Torque Setting	1
Instruction Manual	1
Plastic Case	1



The minimum capacity range of T4MP300 and T6MP300 has been expanded from 60N·m to 40N·m.

### How to Order Torque Setting

Please provide **serial number** and **setting torque** when placing your order.

Calibration Certificate Included

Test Report

Traceability Chart

**serial number**  
T4MP100 in **setting torque**  
100N·m

- CAUTION**
1. Be sure to provide torque unit.
  2. Note that 3 business days is required to set the torque.
  3. Calibration certificate is provided when torque setting is conducted by TONE.

### Expire Date of Calibration Certificate

1. When not in use, the product can stay up to 3 years after calibration date mentioned in the certificate.
2. If the usage started after 3 years from calibration date, it can be used up to 1 year since the first usage or up to 10,000 tightening times.

### Repair·Maintenance

- Inaccuracy may occur if not used for a long time or improprie use of tool. Please contact your distributor regularly for accuracy check.
- Torque devices require regular inspection (once a year or 10,000 times afterwards). Checking service is available with service charge.
- Please contact your distributor in case of experiencing tool malfunction (no clicking sound, slight force, etc.)
- For more information about tool handling, please contact your distributor.
- Accuracy range after repair will be ± 4%.