



# CoroMill® 316 solid carbide head for square shoulder milling

Straight corner radius, center cut

Universal end mills for stability and chip space

CNSC 316..SM..P  
 FHA 0  
 BSG 50°  
 COROMANT



## Metric version

DC	CZC <sub>MS</sub>	APMX	RE	ZEFP	Ordering code	Dimensions							
						1030	1030	1030	1030				
10.00	E10	5.50	0.50	4	316-10SM450-10005P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	0.50	3	316-10SM350-10005P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	1.00	4	316-10SM450-10010P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	1.00	3	316-10SM350-10010P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	1.50	4	316-10SM450-10015P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	2.00	4	316-10SM450-10020P	☆	☆	☆	☆	9.70	5°	12.40	9.70
	E10	5.50	3.00	4	316-10SM450-10030P	☆	☆	☆	☆	9.70	5°	12.40	9.70
12.00	E12	6.50	0.50	3	316-12SM350-12005P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	0.50	4	316-12SM450-12005P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	1.00	4	316-12SM450-12010P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	1.00	3	316-12SM350-12010P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	1.50	4	316-12SM450-12015P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	2.00	4	316-12SM450-12020P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	3.00	4	316-12SM450-12030P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	E12	6.50	4.00	4	316-12SM450-12040P	☆	☆	☆	☆	11.70	5°	14.50	11.70
	16.00	E16	8.50	0.50	4	316-16SM450-16005P	☆	☆	☆	☆	15.50	5°	18.70
E16		8.50	0.50	3	316-16SM350-16005P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	1.00	4	316-16SM450-16010P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	1.00	3	316-16SM350-16010P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	1.50	4	316-16SM450-16015P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	2.00	4	316-16SM450-16020P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	3.00	4	316-16SM450-16030P	☆	☆	☆	☆	15.50	5°	18.70	15.50
E16		8.50	4.00	4	316-16SM450-16040P	☆	☆	☆	☆	15.50	5°	18.70	15.50
20.00		E20	11.00	0.40	6	316-20SM645-20004K	☆	☆	☆	☆	19.30	5°	21.30
	E20	11.00	0.50	3	316-20SM350-20005P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	0.50	4	316-20SM450-20005P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	1.00	3	316-20SM350-20010P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	1.00	4	316-20SM450-20010P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	1.50	4	316-20SM450-20015P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	2.00	4	316-20SM450-20020P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	3.00	4	316-20SM450-20030P	☆	☆	☆	☆	19.30	5°	21.30	19.30
	E20	11.00	4.00	4	316-20SM450-20040P	☆	☆	☆	☆	19.30	5°	21.30	19.30
25.00	E25	13.50	1.00	5	316-25SM550-25010P	☆	☆	☆	☆	24.20	5°	25.60	24.20
	E25	13.50	1.50	5	316-25SM550-25015P	☆	☆	☆	☆	24.20	5°	25.60	24.20
	E25	13.50	2.00	5	316-25SM550-25020P	☆	☆	☆	☆	24.20	5°	25.60	24.20

