



CoroMill® Plura solid carbide square shoulder end mill

Straight, center cut. Hardness $\leq 48\text{HRc}$

End mills for heavy duty milling

CNSC 0
 FHA 42°
 BSG COROMANT
 TCDC h10
 TCDCON h6




Metric version

DC	CZC _{MS}	APMX	CHW	KCH	LU	ZEFP	Ordering code	Dimensions			
								1730	1730	DCON	LF
2.0	6	5.0	0.05	45°	5.0	4	2P342-0200-PA	☆	☆	6.0	57.0
3.0	6	7.0	0.10	45°	7.0	4	2P342-0300-PA	☆	☆	6.0	57.0
4.0	6	9.0	0.10	45°	9.0	4	2P342-0400-PA	☆	☆	6.0	57.0
5.0	6	11.0	0.10	45°	11.0	4	2P342-0500-PA	☆	☆	6.0	57.0
6.0	6	13.0	0.10	45°	13.0	4	2P342-0600-PA	☆	☆	6.0	57.0
8.0	8	18.0	0.15	45°	18.0	4	2P342-0800-PA	☆	☆	8.0	63.0
10.0	10	22.0	0.15	45°	22.0	4	2P342-1000-PA	☆	☆	10.0	72.0
12.0	12	26.0	0.15	45°	26.0	4	2P342-1200-PA	☆	☆	12.0	83.0
14.0	14	30.0	0.15	45°	30.0	4	2P342-1400-PA	☆	☆	14.0	83.0
16.0	16	34.0	0.25	45°	34.0	4	2P342-1600-PA	☆	☆	16.0	92.0
20.0	20	42.0	0.25	45°	42.0	4	2P342-2000-PA	☆	☆	20.0	104.0
25.0	25	52.0	0.25	45°	52.0	4	2P342-2500-PA	☆	☆	25.0	121.0

Inch version

DC	CZC _{MS}	APMX	CHW	KCH	LU	ZEFP	Ordering code	Dimensions, inch			
								1730	1730	DCON	LF
.125	1/8	.313	.004	45°	.313	4	2P342-0318-PA	☆	☆	.125	1.500
.187	3/16	.438	.004	45°	.438	4	2P342-0476-PA	☆	☆	.187	2.000
.250	1/4	.625	.004	45°	.625	4	2P342-0635-PA	☆	☆	.250	2.500
.313	5/16	.750	.004	45°	.750	4	2P342-0794-PA	☆	☆	.313	2.500
.375	3/8	.875	.006	45°	.875	4	2P342-0953-PA	☆	☆	.375	2.500
.438	7/16	1.000	.006	45°	1.000	4	2P342-1111-PA	☆	☆	.438	2.750
.500	1/2	1.125	.006	45°	1.125	4	2P342-1270-PA	☆	☆	.500	3.000
.625	5/8	1.313	.010	45°	1.313	4	2P342-1588-PA	☆	☆	.625	3.500
.750	3/4	1.625	.010	45°	1.625	4	2P342-1905-PA	☆	☆	.750	4.000



L15

