

For Die Handle, see p. 1-424 to 425

The number next to the logo mark indicates items in stock for each brand.




Stock 38,650 Items

Round Die for Unified Thread (Coarse)



T25D-1/4UNC20

- Features**
- Adjustable screw allows you to adjust the dimension.
 - Can also be used when repairing ridge.
- Use**
- Work Material: Iron, Light Metal.
 - For external thread machining.
- Specs**
- Machining Thread: Unified Thread (Coarse)
- Materials**
- Low-Alloy Steel (SKS2)
- Origin**
- Japan



Warning

- Cannot be used for stainless steel screws.

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	SPQ (piece)
480-6077	T25D-1/4UNC20	¥2,293	¥2,830	UNC1/4	20	25	9	10
480-6115	T25D-5/16UNC18	¥2,293	¥2,830	UNC5/16	18	25	9	10
480-6093	T25D-3/8UNC16	¥2,293	¥2,830	UNC3/8	16	25	9	10
480-6131	T25D-7/16UNC14	¥2,293	¥2,830	UNC7/16	14	25	9	10
480-6051	T25D-1/2UNC13	¥2,293	¥2,830	UNC1/2	13	25	9	10
854-9496	T38D-5/8UNC11	¥5,346	¥6,600	UNC5/8	11	38	14	1
854-9516	T50D-3/4UNC10	¥6,829	¥8,430	UNC3/4	10	50	16	1
854-9519	T50D-7/8UNC9	¥6,829	¥8,430	UNC7/8	9	50	16	1
854-9510	T50D-1UNC8	¥6,829	¥8,430	UNC1	8	50	16	1

Contact us:0120-509-849 <http://www.orange-book.com/>




Stock 38,650 Items

Round Die for Unified Thread (Fine)



T25D-1/4UNF28

- Features**
- Adjustable screw allows you to adjust the dimension.
 - Can also be used when repairing ridge.
- Use**
- Work Material: Iron, Light Metal.
 - For external thread machining.
- Specs**
- Machining Thread: Unified Thread (Fine)
- Materials**
- Low-Alloy Steel (SKS2)
- Origin**
- Japan



Warning

- Cannot be used for stainless steel screws.

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	SPQ (piece)
480-6085	T25D-1/4UNF28	¥2,293	¥2,830	UNF1/4	28	25	9	10
480-6123	T25D-5/16UNF24	¥2,293	¥2,830	UNF5/16	24	25	9	10
480-6107	T25D-3/8UNF24	¥2,293	¥2,830	UNF3/8	24	25	9	10
480-6140	T25D-7/16UNF20	¥2,293	¥2,830	UNF7/16	20	25	9	10
480-6069	T25D-1/2UNF20	¥2,293	¥2,830	UNF1/2	20	25	9	10
854-9497	T38D-5/8UNF18	¥5,346	¥6,600	UNF5/8	18	38	14	1
854-9517	T50D-3/4UNF16	¥6,829	¥8,430	UNF3/4	16	50	16	1
854-9520	T50D-7/8UNF14	¥6,829	¥8,430	UNF7/8	14	50	16	1
854-9511	T50D-1UNF12	¥6,829	¥8,430	UNF1	12	50	16	1

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Circular Die for Whitworth Threads



T25D-1/8W40

- Features**
- Adjustable screw allows you to adjust the dimension.
 - Can also be used when repairing ridge.
- Use**
- Work Material: Iron, Light Metal.
 - For external thread machining.
- Specs**
- Machining Thread: Whitworth Thread
- Materials**
- Low-Alloy Steel (SKS2)
- Origin**
- Japan



Warning

- Cannot be used for stainless steel screws.

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
424-9798	T25D-1/8W40	¥2,219	¥2,740	W1/8	40	25	9	10	25
424-9828	T25D-3/16W24	¥2,219	¥2,740	W3/16	24	25	9	10	25
424-9780	T25D-1/4W20	¥2,219	¥2,740	W1/4	20	25	9	10	25
424-9844	T25D-5/16W18	¥2,219	¥2,740	W5/16	18	25	9	10	25
424-9836	T25D-3/8W16	¥2,219	¥2,740	W3/8	16	25	9	10	25
424-9763	T25D-1/2W12	¥2,219	¥2,740	W1/2	12	25	9	10	25
854-9495	T38D-3/8W16	¥5,346	¥6,600	W3/8	16	38	14	1	100
854-9490	T38D-1/2W12	¥5,346	¥6,600	W1/2	12	38	14	1	100
854-9498	T38D-5/8W11	¥5,346	¥6,600	W5/8	11	38	14	1	100
854-9518	T50D-3/4W10	¥6,829	¥8,430	W3/4	10	50	16	1	150
854-9521	T50D-7/8W9	¥6,829	¥8,430	W7/8	9	50	16	1	150
854-9512	T50D-1W8	¥6,829	¥8,430	W1	8	50	16	1	150

Contact us:0120-509-849 <http://www.orange-book.com/>