








CoroTurn® 107 insert for turning

Triangular



	ISO CODE	P					M					K					N					S					ANSI CODE		
		1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	2315	GC15	3005	3205	3210	3215	GC30	H13A	1125	H10	H13A	1105		1115	1125
Finishing		06 5/32																										TCMT 1.2(1.2)0-UF	
																												TCMT 1.2(1.2)1-UF	
		09 7/32																										TCMT 1.8(1.5)1-UF	
																												TCMT 1.8(1.5)2-UF	
		11 1/4																										TCMT 2(1.5)0-UF	
																											TCMT 2(1.5)1-UF		
																											TCMT 2(1.5)2-UF		
	16 3/8																										TCMT 3(2.5)2-UF		
		11 1/4																										TCMT 221-XF	
																												TCMT 222-XF	
Medium		11 1/4																										TCMX 221-WM	
																												TCMX 222-WM	
		16 3/8																										TCMX 3(2.5)2-WM	
		09 7/32																										TCMT 1.8(1.5)1-PM	
																												TCMT 1.8(1.5)2-PM	
		11 1/4																										TCMT 221-PM	
																												TCMT 222-PM	
																												TCMT 223-PM	
		16 3/8																										TCMT 3(2.5)1-PM	
																												TCMT 3(2.5)2-PM	
	22 1/2																										TCMT 3(2.5)3-PM		
																											TCMT 432-PM		
	09 7/32																										TCMT 1.8(1.5)1-MM		
																											TCMT 1.8(1.5)2-MM		
	11 1/4																										TCMT 221-MM		
																											TCMT 222-MM		
	16 3/8																										TCMT 3(2.5)1-MM		
																											TCMT 3(2.5)2-MM		
																											TCMT 3(2.5)3-MM		
	22 1/2																										TCMT 432-MM		
	09 7/32																										TCMT 1.8(1.5)1-KM		
																											TCMT 1.8(1.5)2-KM		
	11 1/4																										TCMT 221-KM		
																											TCMT 222-KM		
	16 3/8																										TCMT 3(2.5)1-KM		
																											TCMT 3(2.5)2-KM		
	22 1/2																										TCMT 3(2.5)3-KM		
																										TCMT 432-KM			

For dimensions, see code key on page I14.

