

The number next to the logo mark indicates items in stock for each brand.



TRUSCO **Stock 38,650 Items**

Tascystey (brass)



TS-13-L (for left)

- Features** • A simple structure to install.
Use • Assistance for furniture and others.
 • Equipment casing.
Materials • Brass
 • Surface Treatment: Nickel-plated Finishing
Origin • Japan



Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Total Length (mm)	Thickness (mm)	Hole Diameter (mm)	Hole Number	SPQ (piece)	Weight (g)
299-9927	TS-13-L	¥565	¥610	For left	150	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	28
299-9935	TS-13-R	¥565	¥610	For right	150	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	28

Contact us:0120-509-849 <http://www.orange-book.com/>







TRUSCO **Stock 38,650 Items**

Tascystey (stainless steel)



TS-43-R (for right)

- Features** • Made of stainless steel and excellent in corrosion resistance.
Use • Assistance for furniture and others.
 • Equipment casing.
Materials • Stainless Steel (SUS304)
Origin • Japan



Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Total Length (mm)	Thickness (mm)	Hole Diameter (mm)	Hole Number	SPQ (piece)	Weight (g)
302-1751	TS-45-L	¥444	¥480	For left	100	1.0	2.5 (plain washer), 2.5 (L washer)	2 (plain washer), 2 (L washer)	10	14
302-1734	TS-44-L	¥537	¥580	For left	150	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	32
302-1718	TS-43-L	¥565	¥610	For left	200	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	35
302-1696	TS-42-L	¥833	¥900	For left	250	1.5	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	61
302-1769	TS-45-R	¥444	¥480	For right	100	1.0	2.5 (plain washer), 2.5 (L washer)	2 (plain washer), 2 (L washer)	10	14
302-1742	TS-44-R	¥537	¥580	For right	150	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	32
302-1726	TS-43-R	¥565	¥610	For right	200	1.2	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	35
302-1700	TS-42-R	¥833	¥900	For right	250	1.5	3.5 (plain washer), 3.5 (L washer)	2 (plain washer), 2 (L washer)	10	61
302-1688	TS-41-LR	¥1,398	¥1,510	Left-right multi-use	300	2.0	3.5 (plain washer)	4 (plain washer)	10	115

Contact us:0120-509-849 <http://www.orange-book.com/>




Stay Mounting Example

Upward Opening Mounting




- Left Mount (L) --- When attached to the left when facing the lid, the folding part folds towards the rear when the lid is closed.
- Right Mount (R) --- When attached to the right when facing the lid, the folding part folds towards the rear when the lid is closed.

Upward Opening Mounting



- Attachment is same as normal folding stays but since the attachment position will differ depending on the specification and opening/closing angle of the lid, make sure to attach it with the right dimension.

Front Opening Mounting



- Left Mount (L) --- When attached to the left when facing the lid, the folding part folds upwards when the lid is closed.
- Right Mount (R) --- When attached to the right when facing the lid, the folding part folds upwards when the lid is closed.
- Attachment is same as normal but make sure to attach it at the position according to the specification and opening/closing angle of the lid.