

Prices displayed include 8% tax.

For Disc Grinders, see p. 5-209 to 226

TRUSCO **Stock 38,650 Items**

## Disc Paper "Diamond Top"



**Com** Drawing SDS  
eco Chemical Content Inspection

- Features** • A Polishing Material for Grinder.  
**Use** • Chamfer of metal titanium, ceramic, carbide alloy, stone, glass etc., flat polishing.  
**Specs** • Max Working Peripheral Velocity: 68m/s (4080m/min)  
**Materials** • Abrasive: Diamond Abrasive Grains  
**Accessories** • 15mm hole adapter (separately sold item no. 5 pieces included: GPTAS-5P)  
**Origin** • Japan



P-S-DT100-11 (mix type)



P-S-DT100-A (all diamond sheet type)

**Mix Type** Features • Since diamond and silicon carbide sheet are mixed, the hit is soft and more economical than all diamond.

Order Unit: 1 Sheet

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per sheet)	MSRP (per sheet)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (sheet)	Weight (g)
216-8391	P-S-DT100-11	100	¥19,857	¥21,450	100	100 x 15 x 16	13000	1	50
216-8405	P-S-DT100-11	180	¥17,006	¥18,370	180	100 x 15 x 16	13000	1	50
216-8413	P-S-DT100-11	400	¥15,062	¥16,270	400	100 x 15 x 16	13000	1	50

**All Diamond Sheet Type** Features • Electrodeposited authentic diamond sheet is used, polishing force and durability are excellent.

Order Unit: 1 Sheet

Order Code	Item No.	OP	Price (per sheet)	MSRP (per sheet)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (sheet)	Weight (g)
216-8367	P-S-DT100-A	100	¥26,383	¥28,500	100	100 x 15 x 16	13000	1	50
216-8375	P-S-DT100-A	180	¥24,300	¥26,250	180	100 x 15 x 16	13000	1	50
216-8383	P-S-DT100-A	400	¥20,829	¥22,500	400	100 x 15 x 16	13000	1	50

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## GP Top Adapter, Small



GPTAS-5P

- Features** • Mounting this adapter converts the hole diameter from 16mm to 15mm.  
**Origin** • Japan

Compatible Disc Paper

GP Top Tokumaru-kun, GP Top, GP Top DX, GP Top Premium, GP Top for Stainless Steel, GP Top Premium Double Flap, Welding Bead Removal Disc, Diamond Top

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
798-4375	GPTAS-5P	¥138	¥170	5	1	6

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## GP Top® 25 Disc Wheel Adapter



GPTA-1P

- Features** • Mounting this adapter converts the hole diameter from 16mm to 15mm.  
**Origin** • Japan

Compatible Disc Paper

GP Top 25, GP Disc Wheel, GP Disc Wheel Soft, GP Nylon Disc, New Nylon Disc

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	SPQ (piece)	Weight (g)
798-4367	GPTA-1P	¥178	¥220	1	7.2

Contact us: 0120-509-849 <http://www.orange-book.com/>

TYROLIT **Stock 93 Items**

## Flap Disc Ceramic



645137

- Features** • Exhibits optimum performance when used on stainless steel.  
 • The whetstone is ground during use to realize a long life.  
**Use** • For grinding work of stainless steel, etc.  
**Specs** • ★★★ Premium type (excellent performance against hard-to-cut materials).  
 • Max Working Peripheral Velocity: 80m/s (4800m/min)  
**Origin** • Czech

Order Unit: 10 Sheets

TYROLIT Company

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Weight (g)
836-7716	645137	¥532*	-*	10	60	125 x 25 x 22.23	12250	48	120
836-9139	34166671	¥532*	-*	10	80	125 x 25 x 22.23	12250	53	195

Contact us: 03-3433-9841

Please order items marked with \* by no. of items in packet.