

Urethane Discs/Sisal Discs

For Disc Grinders, see p. 5-209 to 226/For Oil Polishing Abrasives, see p. 5-1023 to 1025

TRUSCO

TRUSCO


Stock
38,650
Items

"Poly Disc" (for glossing polishing)

RoHS

Com^{eco}
Chemical Content
Inspection

Com
Drawing
SDS



GF100
(non-chromium type oil polishing agent impregnated)

Estimated Unit Price per Sheet
¥3,119

- Features**
- Wool felt disc impregnated with non-chromium type oil-and-fat composition, you can make gloss mirror surface as it is.
 - Saves the trouble of adding a polishing agent.
 - A soft luxury item due to having an added cushioning function.
- Use**
- Optimum for polishing stainless steel, standard metal.
 - Glossing and mirror surface finishing.
- Specs**
- Max Working Peripheral Velocity: 41.9m/s (2512m/min)
 - Max Working Rotation Speed: 8000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan



Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
175-8306	GF100	¥15,593	¥19,250	Polisher	100 x 10 x 16	5	10	250

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

TRUSCO

Stock
38,650
Items

"Soft Power Disc" (made of urethane resin for medium finish polishing)

RoHS

Com^{eco}
Chemical Content
Inspection


Com
Drawing
SDS



SP100C8

Estimated Unit Price per Sheet
¥2,698

- Features**
- Halves the work of creating mirror finished surfaces.
 - With a fine count that could not be realized with paper, final base layer polishing for mirror finishing is possible.
 - A grain size of #600 (equivalent to a finishing surface of #2000).
- Use**
- For partial repairs.
 - Removing burns.
 - Processing before mirror finish work.
- Specs**
- Max Working Peripheral Velocity: 26.2m/s (1570m/min)
 - Max Working Rotation Speed: 5000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan



By rotating, the special foam material and abrasive grain contact the work surface at the same time and start polishing.

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
175-8314	SP100C8	¥13,487	¥16,650	600	100 x 8 x 16	5	10	325

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

TRUSCO

Stock
38,650
Items

"Sisal Disc"

RoHS

Com^{eco}
Chemical Content
Inspection

Com
Drawing
SDS



TSD-100AL

Estimated Unit Price per Sheet
¥1,606

- Features**
- Use it for intermediate polishing of iron and steel, stainless steel, aluminum, etc. with oil-and-fat composition (white bar).
 - Combination set of sisal (Hemp) and cotton cloth.
- Use**
- Intermediate polishing/base polishing of steel, stainless, aluminum and others.
- Specs**
- Max Working Peripheral Velocity: 41.9m/s (2512m/min)
 - Max Working Rotation Speed: 8000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan

Video



Order Unit: 1 Box

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
261-6271	TSD-100	¥8,028	¥9,910	100 x 15 x 16	5	20	425
261-6289	TSD-100AL	¥8,028	¥9,910	100 x 15 x M10 (P1.5)	5	20	440

Contact us:0120-509-849 <http://www.orange-book.com/>

YANASE

YANASE

Stock
585
Items

"SG Sisal Disc"

RoHS



SG-SD100

- Features**
- A saving type for easy one-touch attachment. The disc only can be changed with a single touch while the center cap is attached to the grinder.
 - Please use upon applying a polishing agent (blue bar, white bar, etc.).
- Use**
- For removing burns and polishing prior to creating mirror finishes.
- Specs**
- Max Working Peripheral Velocity: 42m/s (2520m/min)
 - Max Working Rotation Speed: 8000rpm
- Accessories**
- Polishing agent included (1 unit per box)
 - Center cap included (1 piece per box)
- Origin**
- Japan



Order Unit: 5 Sheets

YANASE Co.Ltd

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Outer Diameter x Thickness x Hole Diameter (mm)	Weight (g)
303-0059	SG-SD100	¥1,653*	¥2,450*	5	100 x 15 x 15	67

Contact us:0795-77-2151 <http://www.yanase-saving.com/>