




SV Type (11° Relief)



General Turning and Copying





■ Holder

Above figures show right hand tools.

Cat. No.	Stock		Dimensions (mm)					Applicable Insert
	R	L	h	b	L ₁	f	h ₁	
SVLP R/L1010-H11	●	●	10	10	100	10.5	10	VP□T1103
SVLP R/L1212-H11	●	●	12	12	100	12.5	12	VP□T1103
SVLP R/L1616-H11	●	●	16	16	100	16.5	16	VP□T1103

■ Parts

Screw	Wrench
BFTX02508NV	TRX08
Recommended Tightening Torque (N·m)	
1.5	



■ Holder

Above figures show right hand tools.

Cat. No.	Stock		Dimensions (mm)					Applicable Insert
	R	L	h	b	L ₁	f	h ₁	
SVPP R/L1010-H11	●	●	10	10	100	14.5	10	VP□T1103
SVPP R/L1212-H11	●	●	12	12	100	16.5	12	VP□T1103
SVPP R/L1616-H11	●	●	16	16	100	20.5	16	VP□T1103

■ Parts

Screw	Wrench
BFTX02508NV	TRX08
Recommended Tightening Torque (N·m)	
1.5	

■ Insert (Coated Carbide)

● 11° Relief E-Class

VPET FX		Stock				Dimensions (mm)		
		ACZ150				Inscribed Circle	Thickness	Nose Radius
Cat. No.								
VPET 1103003R-FX	●							0.03
1103003L-FX	●							0.03
110301R-FX	●					6.35	3.18	0.1
110301L-FX	●							0.1
110302R-FX	●							0.2
110302L-FX	●							0.2

VPET FY		Stock				Dimensions (mm)		
		ACZ150				Inscribed Circle	Thickness	Nose Radius
Cat. No.								
VPET 1103003R-FY	●							0.03
1103003L-FY	●							0.03
110301R-FY	●					6.35	3.18	0.1
110301L-FY	●							0.1
110302R-FY	●							0.2
110302L-FY	●							0.2