

Flap Wheels with Shaft (shaft diameter 6mm)

Stock 1,275 Items

5-1033

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Thin Type Flap Wheel (shaft diameter 6mm)

RoHS

Com Drawing SDS



UF3005-80

- Features
- Ideal for fine parts processing and correction work.
 - It can be used for extremely small burr removal work.
 - Thin type allows pinpoint polishing like a pen tip.
- Use
- For polishing of small workpieces.
 - For polishing of fine parts, grooves, and threaded portions, etc.
 - Working Tool: Micro grinder.
- Origin
- Japan

Outer Diameter 30mm Specs •Max Working Rotation Speed: 10000rpm

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
793-3452	UF3005-60	¥2,430	¥3,000	60	30 x 5 x 6 x 40	Approx. 45	5	10	60
793-3479	UF3005-80	¥2,430	¥3,000	80	30 x 5 x 6 x 40	Approx. 47	5	10	60
793-3398	UF3005-100	¥2,430	¥3,000	100	30 x 5 x 6 x 40	Approx. 50	5	10	60
793-3401	UF3005-120	¥2,430	¥3,000	120	30 x 5 x 6 x 40	Approx. 53	5	10	60
793-3410	UF3005-180	¥2,430	¥3,000	180	30 x 5 x 6 x 40	Approx. 55	5	10	60
793-3428	UF3005-240	¥2,430	¥3,000	240	30 x 5 x 6 x 40	Approx. 73	5	10	60
793-3436	UF3005-320	¥2,430	¥3,000	320	30 x 5 x 6 x 40	Approx. 75	5	10	60
793-3444	UF3005-400	¥2,430	¥3,000	400	30 x 5 x 6 x 40	Approx. 75	5	10	60
793-3461	UF3005-600	¥2,430	¥3,000	600	30 x 5 x 6 x 40	Approx. 75	5	10	60




Example

Outer Diameter 40mm Specs •Max Working Rotation Speed: 10000rpm

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
793-3541	UF4005-60	¥2,673	¥3,300	60	40 x 5 x 6 x 40	Approx. 60	5	10	72
793-3568	UF4005-80	¥2,673	¥3,300	80	40 x 5 x 6 x 40	Approx. 63	5	10	72
793-3487	UF4005-100	¥2,673	¥3,300	100	40 x 5 x 6 x 40	Approx. 70	5	10	72
793-3495	UF4005-120	¥2,673	¥3,300	120	40 x 5 x 6 x 40	Approx. 75	5	10	72
793-3509	UF4005-180	¥2,673	¥3,300	180	40 x 5 x 6 x 40	Approx. 80	5	10	72
793-3517	UF4005-240	¥2,673	¥3,300	240	40 x 5 x 6 x 40	Approx. 108	5	10	72
793-3525	UF4005-320	¥2,673	¥3,300	320	40 x 5 x 6 x 40	Approx. 110	5	10	72
793-3533	UF4005-400	¥2,673	¥3,300	400	40 x 5 x 6 x 40	Approx. 110	5	10	72
793-3550	UF4005-600	¥2,673	¥3,300	600	40 x 5 x 6 x 40	Approx. 110	5	10	72



Dimensions

(unit: mm)

Outer Diameter 50mm Specs •Max Working Rotation Speed: 10000rpm

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
793-3631	UF5005-60	¥2,916	¥3,600	60	50 x 5 x 6 x 40	Approx. 85	5	10	92
793-3657	UF5005-80	¥2,916	¥3,600	80	50 x 5 x 6 x 40	Approx. 95	5	10	92
793-3576	UF5005-100	¥2,916	¥3,600	100	50 x 5 x 6 x 40	Approx. 102	5	10	92
793-3584	UF5005-120	¥2,916	¥3,600	120	50 x 5 x 6 x 40	Approx. 108	5	10	92
793-3592	UF5005-180	¥2,916	¥3,600	180	50 x 5 x 6 x 40	Approx. 112	5	10	92
793-3606	UF5005-240	¥2,916	¥3,600	240	50 x 5 x 6 x 40	Approx. 130	5	10	92
793-3614	UF5005-320	¥2,916	¥3,600	320	50 x 5 x 6 x 40	Approx. 145	5	10	92
793-3622	UF5005-400	¥2,916	¥3,600	400	50 x 5 x 6 x 40	Approx. 162	5	10	92
793-3649	UF5005-600	¥2,916	¥3,600	600	50 x 5 x 6 x 40	Approx. 162	5	10	92

Estimated Unit Price per Piece
¥486 to ¥583

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Flap Wheel (shaft diameter 6mm)

RoHS

Com Drawing

Stock Up



UF5025-60-50P

- Features
- A value pack sold in a bundle.
 - For general metal. Since the space between the polishing cloths is somewhat open, it can be used up to the end with less clogging.
 - Inner surface/curved surface/flat surface control and any polishing can be polished freely from soft to hard by adjusting the rotation speed.
 - Use only side. Since it has a shaft, it can be freely used, and the direction of the hair line is also constant.
 - Fits in the shape well of the processing work.
 - Always has a self-regulating effect that can be polished with new abrasive grain surfaces.
 - Heat dissipation effect is large and does not alter the work piece.
- Use
- Commercially available electric grinder, electric drill and drill press.
 - Burring, rust remover, polishing before painting, inner surface curve polishing, metal surface polishing.
 - Working Tool: Straight-type grinder.
- Specs
- Max Working Rotation Speed: 20000rpm
- Origin
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
491-6336	UF2525-60-50P	¥20,493	¥25,300	60	25 x 25 x 6 x 40	Approx. 45	50	1	1580
818-3267	UF2525-80-50P	¥20,493	¥25,300	80	25 x 25 x 6 x 40	Approx. 47	50	1	1580
818-3266	UF2525-120-50P	¥20,493	¥25,300	120	25 x 25 x 6 x 40	Approx. 53	50	1	1580
491-6344	UF3025-60-50P	¥20,493	¥25,300	60	30 x 25 x 6 x 40	Approx. 45	50	1	1700
818-3269	UF3025-80-50P	¥20,493	¥25,300	80	30 x 25 x 6 x 40	Approx. 47	50	1	1700
818-3268	UF3025-120-50P	¥20,493	¥25,300	120	30 x 25 x 6 x 40	Approx. 53	50	1	1700
489-6963	UF4025-60-50P	¥24,867	¥30,700	60	40 x 25 x 6 x 40	Approx. 60	50	1	2375
818-3271	UF4025-80-50P	¥24,867	¥30,700	80	40 x 25 x 6 x 40	Approx. 63	50	1	2375
818-3270	UF4025-120-50P	¥24,867	¥30,700	120	40 x 25 x 6 x 40	Approx. 75	50	1	2375
489-6971	UF5025-60-50P	¥25,353	¥31,300	60	50 x 25 x 6 x 40	Approx. 85	50	1	3330
818-3273	UF5025-80-50P	¥25,353	¥31,300	80	50 x 25 x 6 x 40	Approx. 95	50	1	3330
818-3272	UF5025-120-50P	¥25,353	¥31,300	120	50 x 25 x 6 x 40	Approx. 108	50	1	3330

Estimated Unit Price per Piece
¥410 to ¥508

Contact us: 0120-509-849 <http://www.orange-book.com/>