

Milling Conditions for UDCLBH

WORK MATERIAL			CEMENTED CARBIDE($\geq 87\text{HRA}$) / HARD BRITTLE MATERIALS					CEMENTED CARBIDE($< 87\text{HRA}$)					HARD BRITTLE MATERIALS				
Model Number	Radius of Ball Nose (mm)	Effective Length (mm)	Spindle Speed (min^{-1})	Feed Rate (mm/min)	**Feed Rate 2 (mm/min)	a_p (mm)	a_e (mm)	Spindle Speed (min^{-1})	Feed Rate (mm/min)	**Feed Rate 2 (mm/min)	a_p (mm)	a_e (mm)	Spindle Speed (min^{-1})	Feed Rate (mm/min)	**Feed Rate 2 (mm/min)	a_p (mm)	a_e (mm)
2006-0100	R0.3	1	30,000	600	200	0.03	0.14	30,000	450	150	0.17	0.03	30,000	200	20	0.03	0.14
2006-0150		1.5	30,000	600	200	0.03	0.14	30,000	300	100	0.14	0.025	30,000	200	20	0.03	0.14
2006-0200		2	30,000	300	100	0.022	0.11	30,000	220	70	0.11	0.02	30,000	150	15	0.02	0.11
2006-0300		3	30,000	75	10	0.01	0.08	30,000	75	10	0.08	0.01	30,000	75	10	0.01	0.08
2007-0100	R0.35	1	30,000	690	230	0.035	0.17	30,000	525	260	0.18	0.035	30,000	225	23	0.035	0.17
2008-0200	R0.4	2	30,000	750	250	0.04	0.19	27,000	480	240	0.19	0.04	30,000	250	25	0.04	0.19
2008-0300		3	30,000	350	100	0.037	0.17	25,500	300	100	0.17	0.035	30,000	230	23	0.037	0.17
2008-0400		4	26,000	210	70	0.035	0.16	24,000	210	21	0.16	0.035	30,000	210	21	0.035	0.16
2010-0150	R0.5	1.5	30,000	900	300	0.05	0.22	25,000	650	325	0.2	0.05	30,000	300	30	0.05	0.25
2010-0200		2	30,000	900	300	0.05	0.22	24,000	580	290	0.2	0.05	30,000	300	30	0.05	0.25
2010-0250		2.5	30,000	800	300	0.05	0.22	23,500	520	260	0.2	0.05	30,000	300	30	0.05	0.25
2010-0300		3	30,000	600	200	0.05	0.22	23,000	450	220	0.2	0.05	30,000	300	30	0.05	0.25
2010-0400		4	30,000	400	100	0.05	0.22	21,000	320	160	0.2	0.05	30,000	300	30	0.05	0.25
2010-0500		5	27,000	270	100	0.045	0.2	20,000	250	125	0.2	0.05	27,000	270	30	0.045	0.2
2015-0200	R0.75	2	30,000	1,200	400	0.075	0.27	19,000	750	375	0.23	0.07	24,000	400	45	0.075	0.27
2015-0400		4	30,000	900	250	0.075	0.27	18,000	580	290	0.23	0.07	24,000	350	40	0.075	0.27
2015-0600		6	25,000	500	100	0.075	0.27	17,000	400	200	0.23	0.07	24,000	320	36	0.075	0.27
2020-0300	R1	3	30,000	1,500	500	0.1	0.3	16,500	800	400	0.25	0.1	18,000	600	200	0.1	0.3
2020-0400		4	30,000	1,500	500	0.1	0.3	15,750	750	375	0.25	0.1	18,000	500	160	0.1	0.3
2020-0600		6	20,000	850	280	0.1	0.3	15,000	620	310	0.25	0.1	18,000	400	130	0.1	0.3
2020-0800		8	13,000	400	130	0.1	0.3	14,000	520	260	0.25	0.1	18,000	350	120	0.1	0.3
2020-1000		10	10,000	200	60	0.1	0.3	13,000	420	210	0.25	0.1	18,000	300	100	0.1	0.3

- φ3mm Shank V Series
- UDC-PCD Series
- CBN Series
- Square
- Long Neck Square
- Radius
- Long Neck Radius
- Taper Neck Radius
- Ball / Long Shank Ball
- Long Neck Ball
- Taper Neck Ball
- Taper
- Barrel
- Spiral V Cutter
- Drill
- Technical Data

These milling parameters are based on VF-20, VM-40, VC-70, VU-70 (TAS standard) for Cemented Carbide, and Alumina for Hard Brittle Materials. These are for reference only.

Tool life may differ depending on the type of Cemented Carbide / Hard Brittle Materials.

For best result, fine parameter adjustments may be required, depending on the materials of Cemented Carbide / Hard Brittle Materials; milling shape and strategy; machine rigidity and spindle capability.

**Feed Rate 2 : Feed rate of approach and *connection moves.
*Changing from one engagement point to the next.

