

DISC GRINDER INDUSTRIAL AIR TOOLS

2" (50mm) ANGLE DISC GRINDER




SPINDLE TYPE

U2

Ø 9.53 - 1/4" - 28UNF

Chamfering
& Deburring



Surface
Grinding



SI-AG2-U2P



Palm grip-safety lever

SI-AG2-U2R



Rotary twist switch

Option Attachment

Parts No.243-30




Option Disc Pad

Parts No.129-100

Option Attachment

Parts No.243-W50
2" Grinding Disc

Disc Size : 50×4×9.53mm



Specifications

SI-No.	Free Speed (rpm)	Motor Watt (w)	Noise Level (db) Press/Power	Vibration(m/s ²)		Air Consumption		Air Inlet Size (inch)	Length (mm)	Width (mm)	Height (mm)	Weight (g)
				a	K	CFM	L/Sec					
SI-AG2-U2P	15,000	240	84/95	7.97	1.28	18.4	8.7	1/4	170	68	65	630
SI-AG2-U2R	15,000	240	84/95	7.97	1.28	18.4	8.7	1/4	170	68	65	640

Noise levels according to ISO 15744:2008,ISO 11203:2009