

## Specifications / 規格表

Type	型號/ Model	尺寸/ Dimensions	規格/ Datasheet
反射型 (Reflective) 特殊型 (Other Type)	FRW-11-20 Free cut		*Fiber Type : Flexible *Sensing distance(BR2/L999) : 40mm *Operate temperature : -40°C~+70°C *Minimum bending radius : R1 *Fiber diameter : OD=Ø1.0 ID=Ø0.5
特照型 (Thrubeam)	FT-620 Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 1000mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FTY-420-38G Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 1000mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FTB-320-T80 Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 800mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø1.3 ID=Ø1.0
	FT-320-T004 Free cut		*Fiber Type : Precision *Sensing distance(BR2/L999) : 1000mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FT-320-Q Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 1000mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0

※ : M6 : Toothed Lock Washer Ø11  
 Width Across Flats 10mm, Thickness 2.5mm

※ : M3 : Toothed Lock Washer Ø6.4  
 Width Across Flats 5mm, Thickness 2.2mm